

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859291

Luminaire Tested: **LX4C60D010 EX4C609030 4LBNLI**

Issue Date: 1/21/2022



Test Information

Test Method: LM-79-08
Report Number: P859291
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C60D010 EX4C609030 4LBNLI
Description: 4 INCH 6000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBN TRIM WITH LI FINISH, DIM TO WARM
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5399.2 lumens
Efficiency: N/A
Efficacy: 55.4 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 97.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859291

CATALOG NUMBER: LX4C60D010 EX4C609030 4LBNLI

Luminous Intensity Polar Plot





TEST NUMBER: P859291

CATALOG NUMBER: LX4C60D010 EX4C609030 4LBNLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	92	90	90	90	90
3	105	99	95	92	103	98	94	91	95	92	89	93	90	88	91	89	87	85	85	85	85
4	101	94	89	86	99	93	88	85	91	87	84	89	86	83	87	84	82	81	81	81	81
5	96	89	84	80	95	88	84	80	87	82	79	85	81	79	83	80	78	77	77	77	77
6	92	85	80	76	91	84	79	76	83	78	75	81	78	75	80	77	74	73	73	73	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	69	69	69	69
8	85	77	72	68	84	77	72	68	76	71	68	75	71	68	74	70	67	66	66	66	66
9	82	74	69	65	81	73	68	65	72	68	65	72	68	65	71	67	64	63	63	63	63
10	79	71	66	62	78	70	65	62	69	65	62	69	65	62	68	64	62	61	61	61	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1706988
5°	1536121
10°	1190826
15°	861910
20°	596806
25°	435074
30°	316133
35°	187066
40°	78679
45°	24532
50°	3192
55°	1778
60°	2039
65°	2413
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P859291

CATALOG NUMBER: LX4C60D010 EX4C609030 4LBNLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1095.0	20.3
10°-20°	1874.6	34.7
20°-30°	1489.8	27.6
30°-40°	788.7	14.6
40°-50°	135.9	2.5
50°-60°	10.2	0.2
60°-70°	5.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4459.4	82.6
0°-40°	5248.1	97.2
0°-60°	5394.1	99.9
0°-90°	5399.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5399.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13894	
5°	12456	###
15°	6777	1875
25°	3210	1490
35°	1247	789
45°	141	136
55°	8	10
65°	8	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P859291

CATALOG NUMBER: LX4C60D010 EX4C609030 4LBNLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	13894.5
2.5°	13536.9
5°	12456.1
7.5°	11042.6
10°	9545.8
12.5°	8099.0
15°	6776.7
17.5°	5546.1
20°	4564.9
22.5°	3816.5
25°	3209.6
27.5°	2719.1
30°	2228.5
32.5°	1729.6
35°	1247.3
37.5°	823.3
40°	490.6
42.5°	282.8
45°	141.2
47.5°	50.0
50°	16.7
52.5°	16.7
55°	8.3
57.5°	8.3
60°	8.3
62.5°	8.3
65°	8.3
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)