

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859336

Luminaire Tested: **LX4C65D010 EX4C659027 4LBWH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P859336
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C65D010 EX4C659027 4LBWH
Description: 4 INCH 6500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS
AND 4LBW TRIM WITH H FINISH
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5363.0 lumens
Efficiency: N/A
Efficacy: 74.1 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859336

CATALOG NUMBER: LX4C65D010 EX4C659027 4LBWH

Luminous Intensity Polar Plot





TEST NUMBER: P859336

CATALOG NUMBER: LX4C65D010 EX4C659027 4LBWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91																											
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82																											
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74																											
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67																											
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61																											
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55																											
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50																											
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46																											
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43																											
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	424680
5°	426302
10°	427589
15°	427616
20°	425264
25°	415296
30°	388169
35°	336142
40°	262580
45°	188405
50°	122397
55°	73252
60°	42876
65°	27529
70°	18319
75°	13813
80°	10329
85°	0



TEST NUMBER: P859336

CATALOG NUMBER: LX4C65D010 EX4C659027 4LBWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	329.2	6.1
10°-20°	948.5	17.7
20°-30°	1399.7	26.1
30°-40°	1381.3	25.8
40°-50°	845.3	15.8
50°-60°	324.1	6.0
60°-70°	101.3	1.9
70°-80°	29.7	0.6
80°-90°	4.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2677.4	49.9
0°-40°	4058.7	75.7
0°-60°	5228.0	97.5
0°-90°	5363.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5363.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3457	
5°	3457	329
15°	3362	949
25°	3064	1400
35°	2241	1381
45°	1084	845
55°	342	324
65°	95	101
75°	29	30
85°	0	4
90°	0	



TEST NUMBER: P859336

CATALOG NUMBER: LX4C65D010 EX4C659027 4LBWH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3456.8
2.5°	3464.1
5°	3456.8
7.5°	3449.5
10°	3427.6
12.5°	3398.5
15°	3362.1
17.5°	3318.4
20°	3252.8
22.5°	3180.3
25°	3063.7
27.5°	2918.1
30°	2736.3
32.5°	2510.8
35°	2241.3
37.5°	1942.9
40°	1637.3
42.5°	1353.6
45°	1084.4
47.5°	844.0
50°	640.4
52.5°	473.2
55°	342.0
57.5°	240.1
60°	174.5
62.5°	131.1
65°	94.7
67.5°	72.8
70°	51.0
72.5°	36.4
75°	29.1
77.5°	14.6
80°	14.6
82.5°	7.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)