

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858413

Luminaire Tested: **LD4C15W2N2765D010 4LBNH_5000K**

Issue Date: 11/9/2023



Test Information

Test Method: LM-79-08
Report Number: P858413
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C15W2N2765D010 4LBNH_5000K
Description: 4 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, W2N2765 LEDS
AND 4LBNH TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 934.0 lumens
Efficiency: N/A
Efficacy: 48.6 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 19.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858413

CATALOG NUMBER: LD4C15W2N2765D010 4LBNH_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P858413

CATALOG NUMBER: LD4C15W2N2765D010 4LBNH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	147092
5°	143449
10°	132371
15°	117190
20°	101753
25°	87039
30°	71752
35°	47258
40°	25403
45°	11241
50°	4568
55°	3299
60°	2089
65°	1483
70°	1221
75°	807
80°	1203
85°	0



TEST NUMBER: P858413

CATALOG NUMBER: LD4C15W2N2765D010 4LBNH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.7	11.5
10°-20°	256.8	27.5
20°-30°	294.1	31.5
30°-40°	197.6	21.2
40°-50°	56.5	6.0
50°-60°	13.8	1.5
60°-70°	5.2	0.6
70°-80°	2.0	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	658.6	70.5
0°-40°	856.2	91.7
0°-60°	926.5	99.2
0°-90°	934.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	934.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1197	
5°	1163	108
15°	921	257
25°	642	294
35°	315	198
45°	65	56
55°	15	14
65°	5	5
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P858413

CATALOG NUMBER: LD4C15W2N2765D010 4LBNH_5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1197.3
2.5°	1188.8
5°	1163.2
7.5°	1117.2
10°	1061.1
12.5°	989.5
15°	921.4
17.5°	849.9
20°	778.3
22.5°	710.2
25°	642.1
27.5°	579.0
30°	505.8
32.5°	408.7
35°	315.1
37.5°	229.9
40°	158.4
42.5°	103.9
45°	64.7
47.5°	39.2
50°	23.9
52.5°	18.7
55°	15.4
57.5°	11.9
60°	8.5
62.5°	6.8
65°	5.1
67.5°	3.4
70°	3.4
72.5°	1.7
75°	1.7
77.5°	1.7
80°	1.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)