

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859352

Luminaire Tested: **LX4C65D010 EX4C659030 4LBNH**

Issue Date: 2/8/2022

Test Information

Test Method: LM-79-08
Report Number: P859352
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C65D010 EX4C659030 4LBNH
Description: 4 INCH 6500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBN TRIM WITH H FINISH
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4168.0 lumens
Efficiency: N/A
Efficacy: 57.6 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859352

CATALOG NUMBER: LX4C65D010 EX4C659030 4LBNH

Luminous Intensity Polar Plot





TEST NUMBER: P859352

CATALOG NUMBER: LX4C65D010 EX4C659030 4LBNH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	74	65	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	642905
5°	628588
10°	581204
15°	521519
20°	459086
25°	395085
30°	318161
35°	211797
40°	110177
45°	49881
50°	21635
55°	14522
60°	9312
65°	6599
70°	5424
75°	3607
80°	0
85°	0



TEST NUMBER: P859352

CATALOG NUMBER: LX4C65D010 EX4C659030 4LBNH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	472.1	11.3
10°-20°	1145.3	27.5
20°-30°	1329.7	31.9
30°-40°	880.6	21.1
40°-50°	247.0	5.9
50°-60°	62.1	1.5
60°-70°	23.3	0.6
70°-80°	8.0	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2947.1	70.7
0°-40°	3827.7	91.8
0°-60°	4136.7	99.2
0°-90°	4168.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4168.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5233	
5°	5097	472
15°	4100	1145
25°	2915	1330
35°	1412	881
45°	287	247
55°	68	62
65°	23	23
75°	8	8
85°	0	0
90°	0	



TEST NUMBER: P859352

CATALOG NUMBER: LX4C65D010 EX4C659030 4LBNH

CANDELA DISTRIBUTION (FULL):

	0°
0°	5233.1
2.5°	5210.4
5°	5097.1
7.5°	4900.6
10°	4659.0
12.5°	4387.1
15°	4100.4
17.5°	3820.9
20°	3511.5
22.5°	3224.4
25°	2914.6
27.5°	2620.3
30°	2242.8
32.5°	1842.5
35°	1412.2
37.5°	1011.9
40°	687.0
42.5°	445.4
45°	287.1
47.5°	173.8
50°	113.2
52.5°	83.0
55°	67.8
57.5°	53.0
60°	37.9
62.5°	30.3
65°	22.7
67.5°	15.1
70°	15.1
72.5°	7.6
75°	7.6
77.5°	7.6
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)