

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859354

Luminaire Tested: **LX4C65D010 EX4C659030 4LBSH**

Issue Date: 2/14/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P859354  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/14/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX4C65D010 EX4C659030 4LBSH  
Description: 4 INCH 6500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS  
AND 4LBS TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6552.0 lumens  
Efficiency: N/A  
Efficacy: 90.5 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 72.4  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P859354

CATALOG NUMBER: LX4C65D010 EX4C659030 4LBSH

### Luminous Intensity Polar Plot





TEST NUMBER: P859354

CATALOG NUMBER: LX4C65D010 EX4C659030 4LBSH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77																			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67																			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58																			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51																			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46																			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41																			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37																			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34																			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	420970
5°	419026
10°	410373
15°	395463
20°	377257
25°	356927
30°	336688
35°	317005
40°	298488
45°	278246
50°	253720
55°	224063
60°	189661
65°	148895
70°	106287
75°	58242
80°	10259
85°	0



TEST NUMBER: P859354

CATALOG NUMBER: LX4C65D010 EX4C659030 4LSBH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	321.0	4.9
10°-20°	872.4	13.3
20°-30°	1211.6	18.5
30°-40°	1322.1	20.2
40°-50°	1233.3	18.8
50°-60°	936.1	14.3
60°-70°	512.6	7.8
70°-80°	141.1	2.2
80°-90°	2.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2404.9	36.7
0°-40°	3727.0	56.9
0°-60°	5896.4	90.0
0°-90°	6552.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6552.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3427	
5°	3398	321
15°	3109	872
25°	2633	1212
35°	2114	1322
45°	1602	1233
55°	1046	936
65°	512	513
75°	123	141
85°	0	2
90°	0	



TEST NUMBER: P859354

CATALOG NUMBER: LX4C65D010 EX4C659030 4LBSH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3426.6
2.5°	3426.6
5°	3397.8
7.5°	3354.6
10°	3289.6
12.5°	3203.1
15°	3109.3
17.5°	2993.9
20°	2885.6
22.5°	2755.8
25°	2633.1
27.5°	2510.6
30°	2373.4
32.5°	2243.5
35°	2113.7
37.5°	1983.8
40°	1861.2
42.5°	1731.3
45°	1601.5
47.5°	1471.6
50°	1327.5
52.5°	1190.3
55°	1046.1
57.5°	908.9
60°	771.9
62.5°	634.9
65°	512.2
67.5°	396.7
70°	295.9
72.5°	202.0
75°	122.7
77.5°	57.7
80°	14.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)