

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858431

Luminaire Tested: **LD4C15W2N2765D010 4LBWH\_5000K**

Issue Date: 11/9/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P858431  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 11/9/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD4C15W2N2765D010 4LBWH\_5000K  
Description: 4 INCH 1500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, W2N2765 LEDS  
AND 4LBWH TRIM WITH FINISH  
  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1250.1 lumens  
Efficiency: N/A  
Efficacy: 65.1 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 19.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P858431

CATALOG NUMBER: LD4C15W2N2765D010 4LBWH\_5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P858431

CATALOG NUMBER: LD4C15W2N2765D010 4LBWH\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			
9	67	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	98983
5°	99361
10°	99662
15°	99664
20°	99126
25°	96799
30°	90478
35°	78348
40°	61199
45°	43904
50°	28535
55°	17071
60°	10000
65°	6424
70°	4274
75°	3228
80°	2405
85°	0



TEST NUMBER: P858431

CATALOG NUMBER: LD4C15W2N2765D010 4LBWH\_5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	76.7	6.1
10°-20°	221.1	17.7
20°-30°	326.2	26.1
30°-40°	321.9	25.8
40°-50°	197.0	15.8
50°-60°	75.5	6.0
60°-70°	23.6	1.9
70°-80°	6.9	0.6
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	624.0	49.9
0°-40°	946.0	75.7
0°-60°	1218.6	97.5
0°-90°	1250.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1250.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	806	
5°	806	77
15°	784	221
25°	714	326
35°	522	322
45°	253	197
55°	80	76
65°	22	24
75°	7	7
85°	0	1
90°	0	



TEST NUMBER: P858431

CATALOG NUMBER: LD4C15W2N2765D010 4LBWH\_5000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	805.7
2.5°	807.4
5°	805.7
7.5°	804.0
10°	798.9
12.5°	792.1
15°	783.6
17.5°	773.4
20°	758.2
22.5°	741.3
25°	714.1
27.5°	680.1
30°	637.8
32.5°	585.2
35°	522.4
37.5°	452.9
40°	381.6
42.5°	315.5
45°	252.7
47.5°	196.7
50°	149.3
52.5°	110.3
55°	79.7
57.5°	56.0
60°	40.7
62.5°	30.6
65°	22.1
67.5°	17.0
70°	11.9
72.5°	8.5
75°	6.8
77.5°	3.4
80°	3.4
82.5°	1.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)