

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859374

Luminaire Tested: **LX4C65D010 EX4C659035 4LBNLI**

Issue Date: 1/21/2022



Test Information

Test Method: LM-79-08
Report Number: P859374
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C65D010 EX4C659035 4LBNLI
Description: 4 INCH 6500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 4LBN TRIM WITH LI FINISH
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4980.0 lumens
Efficiency: N/A
Efficacy: 68.8 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859374

CATALOG NUMBER: LX4C65D010 EX4C659035 4LBNLI

Luminous Intensity Polar Plot





TEST NUMBER: P859374

CATALOG NUMBER: LX4C65D010 EX4C659035 4LBNLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	92	90	90	90	90
3	105	99	95	92	103	98	94	91	95	92	89	93	90	88	91	89	87	85	85	85	85
4	101	94	89	86	99	93	88	85	91	87	84	89	86	83	87	84	82	81	81	81	81
5	96	89	84	80	95	88	84	80	87	82	79	85	81	79	83	80	78	77	77	77	77
6	92	85	80	76	91	84	79	76	83	78	75	81	78	75	80	77	74	73	73	73	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	69	69	69	69
8	85	77	72	68	84	77	72	68	76	71	68	75	71	68	74	70	67	66	66	66	66
9	82	74	69	65	81	73	68	65	72	68	65	72	68	65	71	67	64	63	63	63	63
10	79	71	66	62	78	70	65	62	69	65	62	69	65	62	68	64	62	61	61	61	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1574453
5°	1416843
10°	1098362
15°	794984
20°	550459
25°	401307
30°	291591
35°	172548
40°	72569
45°	22621
50°	2943
55°	1649
60°	1892
65°	2238
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P859374

CATALOG NUMBER: LX4C65D010 EX4C659035 4LBNLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1010.0	20.3
10°-20°	1729.0	34.7
20°-30°	1374.2	27.6
30°-40°	727.5	14.6
40°-50°	125.3	2.5
50°-60°	9.4	0.2
60°-70°	4.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4113.2	82.6
0°-40°	4840.6	97.2
0°-60°	4975.3	99.9
0°-90°	4980.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4980.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12816	
5°	11489	###
15°	6250	1729
25°	2960	1374
35°	1150	727
45°	130	125
55°	8	9
65°	8	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P859374

CATALOG NUMBER: LX4C65D010 EX4C659035 4LBNLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	12815.7
2.5°	12485.7
5°	11488.9
7.5°	10185.1
10°	8804.6
12.5°	7470.1
15°	6250.5
17.5°	5115.4
20°	4210.4
22.5°	3520.2
25°	2960.5
27.5°	2508.0
30°	2055.5
32.5°	1595.3
35°	1150.5
37.5°	759.4
40°	452.5
42.5°	260.8
45°	130.2
47.5°	46.1
50°	15.4
52.5°	15.4
55°	7.7
57.5°	7.7
60°	7.7
62.5°	7.7
65°	7.7
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)