

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859415

Luminaire Tested: **LX4C65D010 EX4C659050 4LBNH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P859415
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C65D010 EX4C659050 4LBNH
Description: 4 INCH 6500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS
AND 4LBN TRIM WITH H FINISH
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4319.9 lumens
Efficiency: N/A
Efficacy: 59.7 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859415

CATALOG NUMBER: LX4C65D010 EX4C659050 4LBNH

Luminous Intensity Polar Plot





TEST NUMBER: P859415

CATALOG NUMBER: LX4C65D010 EX4C659050 4LBNH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	74	65	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	666345
5°	651514
10°	602399
15°	540533
20°	475821
25°	409495
30°	329751
35°	219520
40°	114202
45°	51688
50°	22438
55°	15057
60°	9632
65°	6831
70°	5639
75°	3702
80°	0
85°	0



TEST NUMBER: P859415

CATALOG NUMBER: LX4C65D010 EX4C659050 4LBNH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	489.4	11.3
10°-20°	1187.0	27.5
20°-30°	1378.2	31.9
30°-40°	912.7	21.1
40°-50°	256.0	5.9
50°-60°	64.3	1.5
60°-70°	24.2	0.6
70°-80°	8.2	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3054.6	70.7
0°-40°	3967.3	91.8
0°-60°	4287.6	99.3
0°-90°	4319.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4319.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5424	
5°	5283	489
15°	4250	1187
25°	3021	1378
35°	1464	913
45°	298	256
55°	70	64
65°	24	24
75°	8	8
85°	0	0
90°	0	



TEST NUMBER: P859415

CATALOG NUMBER: LX4C65D010 EX4C659050 4LBNH

CANDELA DISTRIBUTION (FULL):

	0°
0°	5423.9
2.5°	5400.4
5°	5283.0
7.5°	5079.3
10°	4828.9
12.5°	4547.1
15°	4249.9
17.5°	3960.2
20°	3639.5
22.5°	3342.0
25°	3020.9
27.5°	2715.9
30°	2324.5
32.5°	1909.7
35°	1463.7
37.5°	1048.8
40°	712.1
42.5°	461.6
45°	297.5
47.5°	180.2
50°	117.4
52.5°	86.0
55°	70.3
57.5°	54.9
60°	39.2
62.5°	31.4
65°	23.5
67.5°	15.7
70°	15.7
72.5°	7.8
75°	7.8
77.5°	7.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)