

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859421

Luminaire Tested: **LX4C65D010 EX4C659050 4LBWLI**

Issue Date: 2/8/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P859421  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/8/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX4C65D010 EX4C659050 4LBWLI  
Description: 4 INCH 6500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS  
AND 4LBW TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver:

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6846.1 lumens  
Efficiency: N/A  
Efficacy: 94.6 lumens/watt  
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct

Input Watts (W): 72.4  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P859421

CATALOG NUMBER: LX4C65D010 EX4C659050 4LBWLI

### Luminous Intensity Polar Plot





TEST NUMBER: P859421

CATALOG NUMBER: LX4C65D010 EX4C659050 4LBWLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92		
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84		
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77		
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70		
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64		
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58		
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54		
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49		
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45		
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42		

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P859421

CATALOG NUMBER: LX4C65D010 EX4C659050 4LBWLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	410.2	6.0
10°-20°	1294.5	18.9
20°-30°	2019.5	29.5
30°-40°	1964.9	28.7
40°-50°	981.4	14.3
50°-60°	151.9	2.2
60°-70°	18.4	0.3
70°-80°	5.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3724.2	54.4
0°-40°	5689.1	83.1
0°-60°	6822.5	99.7
0°-90°	6846.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6846.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4194	
5°	4250	410
15°	4571	1295
25°	4438	2019
35°	3191	1965
45°	1231	981
55°	126	152
65°	16	18
75°	8	5
85°	0	0
90°	0	



TEST NUMBER: P859421

CATALOG NUMBER: LX4C65D010 EX4C659050 4LBWLI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4194.5
2.5°	4210.2
5°	4249.5
7.5°	4312.3
10°	4390.8
12.5°	4492.5
15°	4571.0
17.5°	4633.8
20°	4641.6
22.5°	4586.7
25°	4437.9
27.5°	4218.1
30°	3943.7
32.5°	3599.0
35°	3191.1
37.5°	2744.0
40°	2273.7
42.5°	1772.0
45°	1231.1
47.5°	791.8
50°	478.1
52.5°	258.7
55°	125.6
57.5°	55.0
60°	31.4
62.5°	23.6
65°	15.7
67.5°	15.7
70°	7.9
72.5°	7.9
75°	7.9
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)