

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859448

Luminaire Tested: **LX4C70D010 EX4C709027 4LBWLI**

Issue Date: 2/8/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P859448  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/8/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX4C70D010 EX4C709027 4LBWLI  
Description: 4 INCH 7000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS  
AND 4LBW TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver:

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6673.1 lumens  
Efficiency: N/A  
Efficacy: 85.6 lumens/watt  
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct

Input Watts (W): 78  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P859448

CATALOG NUMBER: LX4C70D010 EX4C709027 4LBWLI

### Luminous Intensity Polar Plot





TEST NUMBER: P859448

CATALOG NUMBER: LX4C70D010 EX4C709027 4LBWLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92	92	92	92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84	84	84	84
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77	77	77	77
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70	70	70	70
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64	64	64	64
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58	58	58	58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54	54	54	54
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49	49	49	49
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45	45	45	45
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42	42	42	42

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P859448

CATALOG NUMBER: LX4C70D010 EX4C709027 4LBWLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	399.8	6.0
10°-20°	1261.8	18.9
20°-30°	1968.4	29.5
30°-40°	1915.3	28.7
40°-50°	956.6	14.3
50°-60°	148.1	2.2
60°-70°	17.9	0.3
70°-80°	5.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3630.1	54.4
0°-40°	5545.4	83.1
0°-60°	6650.1	99.7
0°-90°	6673.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6673.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4088	
5°	4142	400
15°	4456	1262
25°	4326	1968
35°	3110	1915
45°	1200	957
55°	122	148
65°	15	18
75°	8	5
85°	0	0
90°	0	



TEST NUMBER: P859448

CATALOG NUMBER: LX4C70D010 EX4C709027 4LBWLI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4088.5
2.5°	4103.8
5°	4142.1
7.5°	4203.3
10°	4279.8
12.5°	4378.9
15°	4455.5
17.5°	4516.7
20°	4524.3
22.5°	4470.8
25°	4325.7
27.5°	4111.5
30°	3844.0
32.5°	3508.0
35°	3110.5
37.5°	2674.7
40°	2216.2
42.5°	1727.2
45°	1199.9
47.5°	771.8
50°	466.1
52.5°	252.2
55°	122.4
57.5°	53.6
60°	30.6
62.5°	23.0
65°	15.3
67.5°	15.3
70°	7.7
72.5°	7.7
75°	7.7
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)