

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859456

Luminaire Tested: **LD4C70D010 EU4709030 4LBMLI**

Issue Date: 7/19/2024

**Test Information**

Test Method: LM-79-08  
Report Number: P859456  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208178)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/19/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD4C70D010 EU4709030 4LBMLI  
Description: 4 INCH 7000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS  
AND 4LBM TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6574.0 lumens  
Efficiency: N/A  
Efficacy: 84.3 lumens/watt  
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 78  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P859456

CATALOG NUMBER: LD4C70D010 EU4709030 4LBMLI

### Luminous Intensity Polar Plot





TEST NUMBER: P859456

CATALOG NUMBER: LD4C70D010 EU4709030 4LBMLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78
5	94	87	81	77	93	86	81	77	84	79	76	82	78	75	81	77	75	73
6	90	82	76	72	89	81	76	72	80	75	71	78	74	71	77	73	71	69
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65
8	82	73	68	64	81	73	67	64	72	67	64	71	66	63	70	66	63	62
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	67	63	60	58
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	64	60	57	56

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1273192
5°	1251553
10°	1149971
15°	963049
20°	771550
25°	619942
30°	461496
35°	263644
40°	123728
45°	52539
50°	16724
55°	8525
60°	5872
65°	4622
70°	2874
75°	0
80°	0
85°	0



TEST NUMBER: P859456

CATALOG NUMBER: LD4C70D010 EU4709030 4LBMLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	938.3	14.3
10°-20°	2097.8	31.9
20°-30°	2085.7	31.7
30°-40°	1135.8	17.3
40°-50°	262.5	4.0
50°-60°	37.0	0.6
60°-70°	13.7	0.2
70°-80°	3.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5121.8	77.9
0°-40°	6257.6	95.2
0°-60°	6557.2	99.7
0°-90°	6574.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6574.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	10364	
5°	10149	938
15°	7572	2098
25°	4573	2086
35°	1758	1136
45°	302	263
55°	40	37
65°	16	14
75°	0	3
85°	0	0
90°	0	



TEST NUMBER: P859456

CATALOG NUMBER: LD4C70D010 EU4709030 4LBMLI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	10363.5
2.5°	10339.6
5°	10148.6
7.5°	9759.1
10°	9218.3
12.5°	8423.0
15°	7571.9
17.5°	6728.7
20°	5901.5
22.5°	5225.5
25°	4573.4
27.5°	3953.0
30°	3253.2
32.5°	2473.7
35°	1757.9
37.5°	1184.9
40°	771.5
42.5°	485.0
45°	302.4
47.5°	175.1
50°	87.5
52.5°	47.7
55°	39.8
57.5°	23.9
60°	23.9
62.5°	15.9
65°	15.9
67.5°	8.0
70°	8.0
72.5°	8.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)