

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858836

Luminaire Tested: **LX4C05D010 EU4059050 4LBHYLI**

Issue Date: 7/20/2023

Test Information

Test Method: LM-79-08
Report Number: P858836
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2301-896-1)
Test Lab: INNOVATION CENTER
Issue Date: 7/20/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C05D010 EU4059050 4LBHYLI
Description: 4 INCH 500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS AND 4LBHYP TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 534.9 lumens
Efficiency: N/A
Efficacy: 74.3 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.52
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858836

CATALOG NUMBER: LX4C05D010 EU4059050 4LBHYLI

Luminous Intensity Polar Plot





TEST NUMBER: P858836

CATALOG NUMBER: LX4C05D010 EU4059050 4LBHYLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85
5	100	94	89	86	98	93	89	86	91	88	85	89	86	84	88	85	83	82
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79
7	93	87	82	79	92	86	82	79	85	81	78	84	80	78	83	80	78	76
8	91	83	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	74
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	72	71
10	85	78	74	71	84	78	73	71	77	73	70	76	73	70	76	72	70	69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	203323
5°	198192
10°	168024
15°	108910
20°	67631
25°	36396
30°	12512
35°	5039
40°	1347
45°	608
50°	229
55°	107
60°	49
65°	58
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P858836

CATALOG NUMBER: LX4C05D010 EU4059050 4LBHYLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	145.0	27.1
10°-20°	239.1	44.7
20°-30°	123.9	23.2
30°-40°	23.5	4.4
40°-50°	3.0	0.6
50°-60°	0.4	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	508.0	95.0
0°-40°	531.4	99.3
0°-60°	534.8	100.0
0°-90°	534.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	534.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1655	
5°	1607	145
15°	856	239
25°	268	124
35°	34	23
45°	4	3
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P858836

CATALOG NUMBER: LX4C05D010 EU4059050 4LBHYLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1655.0
2.5°	1652.3
5°	1607.1
7.5°	1503.3
10°	1346.9
12.5°	1111.5
15°	856.3
17.5°	650.2
20°	517.3
22.5°	385.6
25°	268.5
27.5°	165.0
30°	88.2
32.5°	59.5
35°	33.6
37.5°	14.6
40°	8.4
42.5°	5.4
45°	3.5
47.5°	2.0
50°	1.2
52.5°	0.5
55°	0.5
57.5°	0.2
60°	0.2
62.5°	0.2
65°	0.2
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)