

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859469

Luminaire Tested: **LX4C70D010 EX4C709030 4LBWLI**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P859469
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C70D010 EX4C709030 4LBWLI
Description: 4 INCH 7000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBW TRIM WITH LI FINISH
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6938.0 lumens
Efficiency: N/A
Efficacy: 88.9 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 78
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859469

CATALOG NUMBER: LX4C70D010 EX4C709030 4LBWLI

Luminous Intensity Polar Plot





TEST NUMBER: P859469

CATALOG NUMBER: LX4C70D010 EX4C709030 4LBWLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92				92															
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84				84															
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77				77															
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70				70															
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64				64															
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58				58															
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54				54															
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49				49															
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45				45															
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42				42															

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P859469

CATALOG NUMBER: LX4C70D010 EX4C709030 4LBWLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	415.7	6.0
10°-20°	1311.9	18.9
20°-30°	2046.6	29.5
30°-40°	1991.3	28.7
40°-50°	994.6	14.3
50°-60°	154.0	2.2
60°-70°	18.6	0.3
70°-80°	5.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3774.2	54.4
0°-40°	5765.6	83.1
0°-60°	6914.2	99.7
0°-90°	6938.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6938.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4251	
5°	4307	416
15°	4632	1312
25°	4498	2047
35°	3234	1991
45°	1248	995
55°	127	154
65°	16	19
75°	8	5
85°	0	0
90°	0	



TEST NUMBER: P859469

CATALOG NUMBER: LX4C70D010 EX4C709030 4LBWLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	4250.9
2.5°	4266.8
5°	4306.6
7.5°	4370.2
10°	4449.8
12.5°	4552.8
15°	4632.4
17.5°	4696.0
20°	4704.0
22.5°	4648.3
25°	4497.5
27.5°	4274.7
30°	3996.7
32.5°	3647.3
35°	3234.0
37.5°	2780.9
40°	2304.3
42.5°	1795.8
45°	1247.6
47.5°	802.4
50°	484.6
52.5°	262.2
55°	127.3
57.5°	55.7
60°	31.8
62.5°	23.9
65°	15.9
67.5°	15.9
70°	8.0
72.5°	8.0
75°	8.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)