

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859503

Luminaire Tested: **LX4C70D010 EX4C709040 4LBMH**

Issue Date: 2/8/2022

Test Information

Test Method: LM-79-08
Report Number: P859503
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C70D010 EX4C709040 4LBMH
Description: 4 INCH 7000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 4LBM TRIM WITH H FINISH
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5351.0 lumens
Efficiency: N/A
Efficacy: 68.6 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 78
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859503

CATALOG NUMBER: LX4C70D010 EX4C709040 4LBMH

Luminous Intensity Polar Plot





TEST NUMBER: P859503

CATALOG NUMBER: LX4C70D010 EX4C709040 4LBMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			91
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			82
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			67
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			61
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			55
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			50
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			46
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			43
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	423722
5°	425340
10°	426641
15°	426662
20°	424310
25°	414374
30°	387303
35°	335392
40°	262003
45°	187988
50°	122110
55°	73103
60°	42778
65°	27471
70°	18283
75°	13813
80°	10259
85°	0



TEST NUMBER: P859503

CATALOG NUMBER: LX4C70D010 EX4C709040 4LBMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	328.5	6.1
10°-20°	946.4	17.7
20°-30°	1396.6	26.1
30°-40°	1378.2	25.8
40°-50°	843.4	15.8
50°-60°	323.3	6.0
60°-70°	101.1	1.9
70°-80°	29.6	0.6
80°-90°	3.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2671.4	49.9
0°-40°	4049.6	75.7
0°-60°	5216.3	97.5
0°-90°	5351.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5351.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3449	
5°	3449	328
15°	3355	946
25°	3057	1397
35°	2236	1378
45°	1082	843
55°	341	323
65°	94	101
75°	29	30
85°	0	4
90°	0	



TEST NUMBER: P859503

CATALOG NUMBER: LX4C70D010 EX4C709040 4LBMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3449.0
2.5°	3456.3
5°	3449.0
7.5°	3441.8
10°	3420.0
12.5°	3390.9
15°	3354.6
17.5°	3310.9
20°	3245.5
22.5°	3173.2
25°	3056.9
27.5°	2911.5
30°	2730.2
32.5°	2505.2
35°	2236.3
37.5°	1938.6
40°	1633.7
42.5°	1350.5
45°	1082.0
47.5°	842.1
50°	638.9
52.5°	472.1
55°	341.3
57.5°	239.5
60°	174.1
62.5°	130.8
65°	94.5
67.5°	72.7
70°	50.9
72.5°	36.3
75°	29.1
77.5°	14.5
80°	14.5
82.5°	7.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)