

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858858

Luminaire Tested: **LX4C05D010 EX4C059827 4LBMDH**

Issue Date: 2/18/2022



Test Information

Test Method: LM-79-08
Report Number: P858858
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-9)
Test Lab: INNOVATION CENTER
Issue Date: 2/18/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C05D010 EX4C059827 4LBMDH
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 398.6 lumens
Efficiency: N/A
Efficacy: 55.4 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.83
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858858

CATALOG NUMBER: LX4C05D010 EX4C059827 4LBMDH

Luminous Intensity Polar Plot





TEST NUMBER: P858858

CATALOG NUMBER: LX4C05D010 EX4C059827 4LBMDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	81			
4	97	90	84	80	95	88	83	79	86	82	78	84	80	77	82	79	77	75			
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70			
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	62	59	66	62	59	57			
9	76	66	60	56	74	65	60	56	64	59	56	64	59	56	63	58	55	54			
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	58994
5°	58196
10°	55463
15°	51333
20°	46203
25°	38389
30°	27904
35°	18087
40°	10937
45°	5647
50°	2561
55°	1542
60°	1032
65°	727
70°	539
75°	380
80°	283
85°	141



TEST NUMBER: P858858

CATALOG NUMBER: LX4C05D010 EX4C059827 4LBMDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.2	11.1
10°-20°	112.6	28.3
20°-30°	127.3	31.9
30°-40°	76.9	19.3
40°-50°	27.0	6.8
50°-60°	6.9	1.7
60°-70°	2.6	0.7
70°-80°	0.9	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	284.1	71.3
0°-40°	361.1	90.6
0°-60°	394.9	99.1
0°-90°	398.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	398.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	480	
5°	472	44
15°	404	113
25°	283	127
35°	121	77
45°	32	27
55°	7	7
65°	2	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P858858

CATALOG NUMBER: LX4C05D010 EX4C059827 4LBMDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	480.2
2.5°	478.2
5°	471.9
7.5°	460.8
10°	444.6
12.5°	425.2
15°	403.6
17.5°	379.8
20°	353.4
22.5°	321.0
25°	283.2
27.5°	239.8
30°	196.7
32.5°	155.5
35°	120.6
37.5°	91.4
40°	68.2
42.5°	49.0
45°	32.5
47.5°	20.0
50°	13.4
52.5°	9.6
55°	7.2
57.5°	5.5
60°	4.2
62.5°	3.3
65°	2.5
67.5°	2.0
70°	1.5
72.5°	1.1
75°	0.8
77.5°	0.5
80°	0.4
82.5°	0.2
85°	0.1
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)