

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858884

Luminaire Tested: **LX4C05D010 EX4C059835 4LBMDH**

Issue Date: 2/18/2022



Test Information

Test Method: LM-79-08
Report Number: P858884
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-9)
Test Lab: INNOVATION CENTER
Issue Date: 2/18/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C05D010 EX4C059835 4LBMDH
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 420.9 lumens
Efficiency: N/A
Efficacy: 58.5 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.83
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858884

CATALOG NUMBER: LX4C05D010 EX4C059835 4LBMDH

Luminous Intensity Polar Plot





TEST NUMBER: P858884

CATALOG NUMBER: LX4C05D010 EX4C059835 4LBMDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | |
| 1 | 113 | 111 | 108 | 106 | 111 | 109 | 106 | 104 | 104 | 103 | 101 | 101 | 99 | 98 | 97 | 96 | 95 | 93 | | | |
| 2 | 108 | 103 | 99 | 95 | 106 | 101 | 97 | 94 | 98 | 95 | 92 | 95 | 92 | 90 | 92 | 90 | 88 | 87 | | | |
| 3 | 102 | 96 | 91 | 87 | 100 | 94 | 90 | 86 | 92 | 88 | 85 | 89 | 86 | 83 | 87 | 84 | 82 | 81 | | | |
| 4 | 97 | 90 | 84 | 80 | 95 | 88 | 83 | 79 | 86 | 82 | 78 | 84 | 80 | 77 | 82 | 79 | 77 | 75 | | | |
| 5 | 92 | 84 | 78 | 74 | 91 | 83 | 77 | 73 | 81 | 76 | 73 | 79 | 75 | 72 | 78 | 74 | 71 | 70 | | | |
| 6 | 88 | 79 | 73 | 68 | 86 | 78 | 72 | 68 | 76 | 71 | 68 | 75 | 71 | 67 | 74 | 70 | 67 | 65 | | | |
| 7 | 83 | 74 | 68 | 64 | 82 | 73 | 68 | 64 | 72 | 67 | 63 | 71 | 66 | 63 | 70 | 66 | 63 | 61 | | | |
| 8 | 79 | 70 | 64 | 60 | 78 | 69 | 63 | 60 | 68 | 63 | 59 | 67 | 62 | 59 | 66 | 62 | 59 | 57 | | | |
| 9 | 76 | 66 | 60 | 56 | 74 | 65 | 60 | 56 | 64 | 59 | 56 | 64 | 59 | 56 | 63 | 58 | 55 | 54 | | | |
| 10 | 72 | 62 | 57 | 53 | 71 | 62 | 56 | 53 | 61 | 56 | 53 | 60 | 56 | 52 | 60 | 55 | 52 | 51 | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 62287 |
| 5° | 61452 |
| 10° | 58570 |
| 15° | 54207 |
| 20° | 48791 |
| 25° | 40531 |
| 30° | 29464 |
| 35° | 19092 |
| 40° | 11563 |
| 45° | 5942 |
| 50° | 2695 |
| 55° | 1628 |
| 60° | 1106 |
| 65° | 785 |
| 70° | 575 |
| 75° | 380 |
| 80° | 283 |
| 85° | 141 |



TEST NUMBER: P858884

CATALOG NUMBER: LX4C05D010 EX4C059835 4LBMDH

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 46.6 | 11.1 |
| 10°-20° | 118.9 | 28.2 |
| 20°-30° | 134.5 | 31.9 |
| 30°-40° | 81.3 | 19.3 |
| 40°-50° | 28.5 | 6.8 |
| 50°-60° | 7.3 | 1.7 |
| 60°-70° | 2.8 | 0.7 |
| 70°-80° | 0.9 | 0.2 |
| 80°-90° | 0.2 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 300.0 | 71.3 |
| 0°-40° | 381.3 | 90.6 |
| 0°-60° | 417.0 | 99.1 |
| 0°-90° | 420.9 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 420.9 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 507 | |
| 5° | 498 | 47 |
| 15° | 426 | 119 |
| 25° | 299 | 134 |
| 35° | 127 | 81 |
| 45° | 34 | 28 |
| 55° | 8 | 7 |
| 65° | 3 | 3 |
| 75° | 1 | 1 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P858884

CATALOG NUMBER: LX4C05D010 EX4C059835 4LBMDH

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|-------|
| 0° | 507.0 |
| 2.5° | 505.0 |
| 5° | 498.3 |
| 7.5° | 486.5 |
| 10° | 469.5 |
| 12.5° | 449.0 |
| 15° | 426.2 |
| 17.5° | 401.0 |
| 20° | 373.2 |
| 22.5° | 339.0 |
| 25° | 299.0 |
| 27.5° | 253.2 |
| 30° | 207.7 |
| 32.5° | 164.2 |
| 35° | 127.3 |
| 37.5° | 96.6 |
| 40° | 72.1 |
| 42.5° | 51.8 |
| 45° | 34.2 |
| 47.5° | 21.1 |
| 50° | 14.1 |
| 52.5° | 10.2 |
| 55° | 7.6 |
| 57.5° | 5.8 |
| 60° | 4.5 |
| 62.5° | 3.5 |
| 65° | 2.7 |
| 67.5° | 2.1 |
| 70° | 1.6 |
| 72.5° | 1.2 |
| 75° | 0.8 |
| 77.5° | 0.6 |
| 80° | 0.4 |
| 82.5° | 0.3 |
| 85° | 0.1 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)