

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858886

Luminaire Tested: **LX4C05D010 EX4C059835 4LBMH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P858886
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C05D010 EX4C059835 4LBMH
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 444.9 lumens
Efficiency: N/A
Efficacy: 61.8 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858886

CATALOG NUMBER: LX4C05D010 EX4C059835 4LBMH

Luminous Intensity Polar Plot





TEST NUMBER: P858886

CATALOG NUMBER: LX4C05D010 EX4C059835 4LBMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91																			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82																			
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74																			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67																			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61																			
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55																			
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50																			
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46																			
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43																			
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	35234
5°	35369
10°	35479
15°	35473
20°	35286
25°	34458
30°	32202
35°	27881
40°	21779
45°	15637
50°	10149
55°	6083
60°	3538
65°	2267
70°	1509
75°	1139
80°	849
85°	0



TEST NUMBER: P858886

CATALOG NUMBER: LX4C05D010 EX4C059835 4LBMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	27.3	6.1
10°-20°	78.7	17.7
20°-30°	116.1	26.1
30°-40°	114.6	25.8
40°-50°	70.1	15.8
50°-60°	26.9	6.0
60°-70°	8.4	1.9
70°-80°	2.4	0.6
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	222.2	49.9
0°-40°	336.7	75.7
0°-60°	433.7	97.5
0°-90°	444.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	444.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	287	
5°	287	27
15°	279	79
25°	254	116
35°	186	115
45°	90	70
55°	28	27
65°	8	8
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P858886

CATALOG NUMBER: LX4C05D010 EX4C059835 4LBMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	286.8
2.5°	287.4
5°	286.8
7.5°	286.2
10°	284.4
12.5°	282.0
15°	278.9
17.5°	275.4
20°	269.9
22.5°	263.9
25°	254.2
27.5°	242.1
30°	227.0
32.5°	208.3
35°	185.9
37.5°	161.2
40°	135.8
42.5°	112.3
45°	90.0
47.5°	70.0
50°	53.1
52.5°	39.2
55°	28.4
57.5°	19.9
60°	14.4
62.5°	10.9
65°	7.8
67.5°	6.1
70°	4.2
72.5°	3.0
75°	2.4
77.5°	1.2
80°	1.2
82.5°	0.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)