

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859544

Luminaire Tested: **LX4C75D010 EX4C759027 4LBMH**

Issue Date: 2/8/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P859544  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/8/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX4C75D010 EX4C759027 4LBMH  
Description: 4 INCH 7500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS  
AND 4LBM TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver:


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5959.0 lumens  
Efficiency: N/A  
Efficacy: 73.1 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 81.5  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P859544

CATALOG NUMBER: LX4C75D010 EX4C759027 4LBMH

### Luminous Intensity Polar Plot





TEST NUMBER: P859544

CATALOG NUMBER: LX4C75D010 EX4C759027 4LBMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			91
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			82
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			67
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			61
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			55
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			50
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			46
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			43
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			39

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	471868
5°	473670
10°	475118
15°	475134
20°	472526
25°	461452
30°	431308
35°	373501
40°	291768
45°	209341
50°	135986
55°	81392
60°	47643
65°	30581
70°	20367
75°	15379
80°	11461
85°	0



TEST NUMBER: P859544

CATALOG NUMBER: LX4C75D010 EX4C759027 4LBMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	365.8	6.1
10°-20°	1053.9	17.7
20°-30°	1555.2	26.1
30°-40°	1534.8	25.8
40°-50°	939.2	15.8
50°-60°	360.0	6.0
60°-70°	112.6	1.9
70°-80°	33.0	0.6
80°-90°	4.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2974.9	49.9
0°-40°	4509.7	75.7
0°-60°	5809.0	97.5
0°-90°	5959.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5959.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3841	
5°	3841	366
15°	3736	1054
25°	3404	1555
35°	2490	1535
45°	1205	939
55°	380	360
65°	105	113
75°	32	33
85°	0	4
90°	0	



TEST NUMBER: P859544

CATALOG NUMBER: LX4C75D010 EX4C759027 4LBMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3840.9
2.5°	3849.0
5°	3840.9
7.5°	3832.8
10°	3808.6
12.5°	3776.2
15°	3735.7
17.5°	3687.1
20°	3614.3
22.5°	3533.7
25°	3404.2
27.5°	3242.3
30°	3040.4
32.5°	2789.8
35°	2490.4
37.5°	2158.9
40°	1819.3
42.5°	1504.0
45°	1204.9
47.5°	937.8
50°	711.5
52.5°	525.7
55°	380.0
57.5°	266.7
60°	193.9
62.5°	145.7
65°	105.2
67.5°	80.9
70°	56.7
72.5°	40.5
75°	32.4
77.5°	16.2
80°	16.2
82.5°	8.1
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)