

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858891

Luminaire Tested: **LX4C05D010 EX4C059835 4LBSLI**

Issue Date: 2/9/2022



Test Information

Test Method: LM-79-08
Report Number: P858891
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208407)
Test Lab: INNOVATION CENTER
Issue Date: 2/9/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C05D010 EX4C059835 4LBSLI
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 605.4 lumens
Efficiency: N/A
Efficacy: 84.1 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858891

CATALOG NUMBER: LX4C05D010 EX4C059835 4LBSLI

Luminous Intensity Polar Plot





TEST NUMBER: P858891

CATALOG NUMBER: LX4C05D010 EX4C059835 4LBSLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90			
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80			
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71			
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63			
5	84	73	66	61	82	72	65	60	70	64	60	69	63	59	67	62	59	57			
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51			
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46			
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42			
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39			
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	53110
5°	51907
10°	48752
15°	45355
20°	42058
25°	38348
30°	34145
35°	30250
40°	27199
45°	24341
50°	20871
55°	16792
60°	12506
65°	7994
70°	3843
75°	617
80°	424
85°	0



TEST NUMBER: P858891

CATALOG NUMBER: LX4C05D010 EX4C059835 4LBSLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.2	6.5
10°-20°	100.0	16.5
20°-30°	129.6	21.4
30°-40°	126.9	21.0
40°-50°	107.6	17.8
50°-60°	70.5	11.6
60°-70°	28.4	4.7
70°-80°	3.2	0.5
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	268.7	44.4
0°-40°	395.7	65.4
0°-60°	573.8	94.8
0°-90°	605.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	605.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	432	
5°	421	39
15°	357	100
25°	283	130
35°	202	127
45°	140	108
55°	78	71
65°	28	28
75°	1	3
85°	0	0
90°	0	



TEST NUMBER: P858891

CATALOG NUMBER: LX4C05D010 EX4C059835 4LBSLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	432.3
2.5°	429.0
5°	420.9
7.5°	407.5
10°	390.8
12.5°	372.7
15°	356.6
17.5°	339.2
20°	321.7
22.5°	303.0
25°	282.9
27.5°	262.1
30°	240.7
32.5°	220.5
35°	201.7
37.5°	186.4
40°	169.6
42.5°	154.8
45°	140.1
47.5°	124.7
50°	109.2
52.5°	93.8
55°	78.4
57.5°	64.4
60°	50.9
62.5°	38.9
65°	27.5
67.5°	18.1
70°	10.7
72.5°	4.7
75°	1.3
77.5°	0.6
80°	0.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)