

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858903

Luminaire Tested: **LX4C05D010 EX4C059840 4LBSH**

Issue Date: 2/14/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P858903  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/14/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX4C05D010 EX4C059840 4LBSH  
Description:  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 581.3 lumens  
Efficiency: N/A  
Efficacy: 80.7 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.2  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P858903

CATALOG NUMBER: LX4C05D010 EX4C059840 4LBSH

### Luminous Intensity Polar Plot





TEST NUMBER: P858903

CATALOG NUMBER: LX4C05D010 EX4C059840 4LBSH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	37360
5°	37182
10°	36427
15°	35091
20°	33482
25°	31665
30°	29875
35°	28121
40°	26494
45°	24689
50°	22515
55°	19877
60°	16831
65°	13227
70°	9411
75°	5174
80°	849
85°	0



TEST NUMBER: P858903

CATALOG NUMBER: LX4C05D010 EX4C059840 4LSBH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	28.5	4.9
10°-20°	77.4	13.3
20°-30°	107.5	18.5
30°-40°	117.3	20.2
40°-50°	109.4	18.8
50°-60°	83.0	14.3
60°-70°	45.5	7.8
70°-80°	12.5	2.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	213.4	36.7
0°-40°	330.7	56.9
0°-60°	523.2	90.0
0°-90°	581.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	581.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	304	
5°	302	28
15°	276	77
25°	234	108
35°	188	117
45°	142	109
55°	93	83
65°	46	46
75°	11	12
85°	0	0
90°	0	



TEST NUMBER: P858903

CATALOG NUMBER: LX4C05D010 EX4C059840 4LBSH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	304.1
2.5°	304.1
5°	301.5
7.5°	297.7
10°	292.0
12.5°	284.2
15°	275.9
17.5°	265.6
20°	256.1
22.5°	244.5
25°	233.6
27.5°	222.8
30°	210.6
32.5°	199.1
35°	187.5
37.5°	176.0
40°	165.2
42.5°	153.6
45°	142.1
47.5°	130.6
50°	117.8
52.5°	105.6
55°	92.8
57.5°	80.6
60°	68.5
62.5°	56.4
65°	45.5
67.5°	35.2
70°	26.2
72.5°	17.9
75°	10.9
77.5°	5.1
80°	1.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)