

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859560

Luminaire Tested: **LX4C75D010 EX4C759030 4LBNH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P859560
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C75D010 EX4C759030 4LBNH
Description: 4 INCH 7500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBN TRIM WITH H FINISH
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5148.1 lumens
Efficiency: N/A
Efficacy: 63.2 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 81.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859560

CATALOG NUMBER: LX4C75D010 EX4C759030 4LBNH

Luminous Intensity Polar Plot





TEST NUMBER: P859560

CATALOG NUMBER: LX4C75D010 EX4C759030 4LBNH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	74	65	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	794063
5°	776391
10°	717854
15°	644140
20°	567024
25°	487980
30°	392964
35°	261604
40°	136077
45°	61609
50°	26739
55°	17928
60°	11499
65°	8169
70°	6717
75°	4462
80°	0
85°	0



TEST NUMBER: P859560

CATALOG NUMBER: LX4C75D010 EX4C759030 4LBNH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	583.2	11.3
10°-20°	1414.6	27.5
20°-30°	1642.3	31.9
30°-40°	1087.6	21.1
40°-50°	305.1	5.9
50°-60°	76.7	1.5
60°-70°	28.8	0.6
70°-80°	9.9	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3640.0	70.7
0°-40°	4727.7	91.8
0°-60°	5109.4	99.2
0°-90°	5148.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5148.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6464	
5°	6296	583
15°	5064	1415
25°	3600	1642
35°	1744	1088
45°	355	305
55°	84	77
65°	28	29
75°	9	10
85°	0	0
90°	0	



TEST NUMBER: P859560

CATALOG NUMBER: LX4C75D010 EX4C759030 4LBNH

CANDELA DISTRIBUTION (FULL):

	0°
0°	6463.5
2.5°	6435.5
5°	6295.6
7.5°	6052.9
10°	5754.4
12.5°	5418.6
15°	5064.5
17.5°	4719.3
20°	4337.1
22.5°	3982.5
25°	3599.9
27.5°	3236.4
30°	2770.1
32.5°	2275.7
35°	1744.3
37.5°	1249.9
40°	848.5
42.5°	550.1
45°	354.6
47.5°	214.7
50°	139.9
52.5°	102.5
55°	83.7
57.5°	65.5
60°	46.8
62.5°	37.4
65°	28.1
67.5°	18.7
70°	18.7
72.5°	9.4
75°	9.4
77.5°	9.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)