

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858943

Luminaire Tested: **LX4C05D010 EX4C059030 4LBSLI**

Issue Date: 2/9/2022

**Test Information**

Test Method: LM-79-08  
Report Number: P858943  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208407)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/9/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX4C05D010 EX4C059030 4LBSLI  
Description: 4 INCH 500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS AND  
4LBS TRIM WITH LI FINISH, DIM TO WARM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 681.5 lumens  
Efficiency: N/A  
Efficacy: 94.6 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.2  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P858943

CATALOG NUMBER: LX4C05D010 EX4C059030 4LBSLI

### Luminous Intensity Polar Plot





TEST NUMBER: P858943

CATALOG NUMBER: LX4C05D010 EX4C059030 4LBSLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |    |    |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |    | 0  |     |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    | 100 |
| 1   | 112 | 108 | 105 | 102 | 109 | 106 | 103 | 101 | 102 | 100 | 98  | 98  | 96  | 95  | 95  | 93  | 92  | 90  |    |    | 90  |
| 2   | 104 | 98  | 93  | 88  | 102 | 96  | 91  | 87  | 93  | 89  | 85  | 90  | 86  | 84  | 87  | 84  | 82  | 80  |    |    | 80  |
| 3   | 97  | 89  | 82  | 77  | 95  | 87  | 81  | 77  | 84  | 79  | 75  | 82  | 78  | 74  | 79  | 76  | 73  | 71  |    |    | 71  |
| 4   | 90  | 81  | 73  | 68  | 88  | 79  | 73  | 68  | 77  | 71  | 67  | 75  | 70  | 66  | 73  | 69  | 65  | 63  |    |    | 63  |
| 5   | 84  | 73  | 66  | 61  | 82  | 72  | 65  | 60  | 70  | 64  | 60  | 69  | 63  | 59  | 67  | 62  | 59  | 57  |    |    | 57  |
| 6   | 79  | 67  | 60  | 54  | 77  | 66  | 59  | 54  | 65  | 58  | 54  | 63  | 58  | 53  | 62  | 57  | 53  | 51  |    |    | 51  |
| 7   | 74  | 62  | 54  | 49  | 72  | 61  | 54  | 49  | 60  | 53  | 49  | 58  | 53  | 48  | 57  | 52  | 48  | 46  |    |    | 46  |
| 8   | 69  | 57  | 50  | 45  | 68  | 57  | 50  | 45  | 55  | 49  | 45  | 54  | 49  | 44  | 53  | 48  | 44  | 42  |    |    | 42  |
| 9   | 65  | 53  | 46  | 41  | 64  | 53  | 46  | 41  | 52  | 45  | 41  | 51  | 45  | 41  | 50  | 44  | 41  | 39  |    |    | 39  |
| 10  | 61  | 50  | 43  | 38  | 60  | 49  | 42  | 38  | 48  | 42  | 38  | 47  | 42  | 38  | 46  | 41  | 37  | 36  |    |    | 36  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 59781 |
| 5°  | 58430 |
| 10° | 54864 |
| 15° | 51053 |
| 20° | 47340 |
| 25° | 43160 |
| 30° | 38430 |
| 35° | 34045 |
| 40° | 30599 |
| 45° | 27399 |
| 50° | 23509 |
| 55° | 18913 |
| 60° | 14104 |
| 65° | 8983  |
| 70° | 4346  |
| 75° | 712   |
| 80° | 495   |
| 85° | 0     |



TEST NUMBER: P858943

CATALOG NUMBER: LX4C05D010 EX4C059030 4LBSLI

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 44.1   | 6.5       |
| 10°-20°   | 112.5  | 16.5      |
| 20°-30°   | 145.8  | 21.4      |
| 30°-40°   | 142.9  | 21.0      |
| 40°-50°   | 121.1  | 17.8      |
| 50°-60°   | 79.4   | 11.7      |
| 60°-70°   | 31.9   | 4.7       |
| 70°-80°   | 3.6    | 0.5       |
| 80°-90°   | 0.1    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 302.5  | 44.4      |
| 0°-40°    | 445.3  | 65.4      |
| 0°-60°    | 645.8  | 94.8      |
| 0°-90°    | 681.5  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 681.5  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 487 |      |
| 5°  | 474 | 44   |
| 15° | 401 | 113  |
| 25° | 318 | 146  |
| 35° | 227 | 143  |
| 45° | 158 | 121  |
| 55° | 88  | 79   |
| 65° | 31  | 32   |
| 75° | 2   | 4    |
| 85° | 0   | 0    |
| 90° | 0   |      |



TEST NUMBER: P858943

CATALOG NUMBER: LX4C05D010 EX4C059030 4LBSLI

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 486.6 |
| 2.5°  | 482.9 |
| 5°    | 473.8 |
| 7.5°  | 458.7 |
| 10°   | 439.8 |
| 12.5° | 419.5 |
| 15°   | 401.4 |
| 17.5° | 381.8 |
| 20°   | 362.1 |
| 22.5° | 341.1 |
| 25°   | 318.4 |
| 27.5° | 295.0 |
| 30°   | 270.9 |
| 32.5° | 248.2 |
| 35°   | 227.0 |
| 37.5° | 209.7 |
| 40°   | 190.8 |
| 42.5° | 174.2 |
| 45°   | 157.7 |
| 47.5° | 140.4 |
| 50°   | 123.0 |
| 52.5° | 105.6 |
| 55°   | 88.3  |
| 57.5° | 72.4  |
| 60°   | 57.4  |
| 62.5° | 43.7  |
| 65°   | 30.9  |
| 67.5° | 20.3  |
| 70°   | 12.1  |
| 72.5° | 5.3   |
| 75°   | 1.5   |
| 77.5° | 0.7   |
| 80°   | 0.7   |
| 82.5° | 0.0   |
| 85°   | 0.0   |
| 87.5° | 0.0   |
| 90°   | 0.0   |



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)