

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859591

Luminaire Tested: **LX4C75D010 EX4C759040 4LBSLI**

Issue Date: 2/9/2022



Test Information

Test Method: LM-79-08
Report Number: P859591
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208407)
Test Lab: INNOVATION CENTER
Issue Date: 2/9/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C75D010 EX4C759040 4LBSLI
Description: 4 INCH 7500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 4LBS TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8570.9 lumens
Efficiency: N/A
Efficacy: 105.2 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 81.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859591

CATALOG NUMBER: LX4C75D010 EX4C759040 4LBSLI

Luminous Intensity Polar Plot





TEST NUMBER: P859591

CATALOG NUMBER: LX4C75D010 EX4C759040 4LBSLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90	90	90	90
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80	80	80	80
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71	71	71	71
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63	63	63	63
5	84	73	66	61	82	72	65	60	70	64	60	69	63	59	67	62	59	57	57	57	57
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51	51	51	51
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46	46	46	46
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42	42	42	42
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39	39	39	39
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36	36	36	36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	751863
5°	734831
10°	690060
15°	642003
20°	595433
25°	542785
30°	483228
35°	428318
40°	384977
45°	344546
50°	295576
55°	237771
60°	177155
65°	113110
70°	54491
75°	9019
80°	6650
85°	0



TEST NUMBER: P859591

CATALOG NUMBER: LX4C75D010 EX4C759040 4LBSLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	554.9	6.5
10°-20°	1415.3	16.5
20°-30°	1833.9	21.4
30°-40°	1796.9	21.0
40°-50°	1523.1	17.8
50°-60°	998.4	11.6
60°-70°	401.3	4.7
70°-80°	45.8	0.5
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3804.1	44.4
0°-40°	5601.0	65.3
0°-60°	8122.5	94.8
0°-90°	8570.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8570.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6120	
5°	5959	555
15°	5048	1415
25°	4004	1834
35°	2856	1797
45°	1983	1523
55°	1110	998
65°	389	401
75°	19	46
85°	0	1
90°	0	



TEST NUMBER: P859591

CATALOG NUMBER: LX4C75D010 EX4C759040 4LBSLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	6120.0
2.5°	6072.5
5°	5958.6
7.5°	5768.8
10°	5531.6
12.5°	5275.5
15°	5047.7
17.5°	4801.2
20°	4554.4
22.5°	4288.8
25°	4004.2
27.5°	3709.9
30°	3406.4
32.5°	3121.7
35°	2855.9
37.5°	2637.8
40°	2400.5
42.5°	2191.8
45°	1983.1
47.5°	1764.8
50°	1546.5
52.5°	1328.4
55°	1110.1
57.5°	910.9
60°	721.0
62.5°	550.3
65°	389.1
67.5°	256.2
70°	151.7
72.5°	66.3
75°	19.0
77.5°	9.4
80°	9.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)