

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858923

Luminaire Tested: **LX4C05D010 EX4C059030 4LBMDH**

Issue Date: 2/18/2022

**Test Information**

Test Method: LM-79-08  
Report Number: P858923  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/18/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX4C05D010 EX4C059030 4LBMDH  
Description: 4 INCH 500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS AND 4LRMD45 TRIM WITH H FINISH, DIM TO WARM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 465.0 lumens  
Efficiency: N/A  
Efficacy: 64.6 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.83  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.2  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P858923

CATALOG NUMBER: LX4C05D010 EX4C059030 4LBMDH

### Luminous Intensity Polar Plot





TEST NUMBER: P858923

CATALOG NUMBER: LX4C05D010 EX4C059030 4LBMDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	81			
4	97	90	84	80	95	88	83	79	86	82	78	84	80	77	82	79	77	75			
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70			
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	63	60	68	63	59	67	62	59	66	62	59	57			
9	76	66	60	56	74	65	60	56	64	59	56	64	59	56	63	58	55	54			
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	68823
5°	67889
10°	64707
15°	59880
20°	53903
25°	44773
30°	32557
35°	21102
40°	12766
45°	6585
50°	2982
55°	1799
60°	1204
65°	872
70°	647
75°	427
80°	283
85°	141



TEST NUMBER: P858923

CATALOG NUMBER: LX4C05D010 EX4C059030 4LBMDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	51.5	11.1
10°-20°	131.4	28.3
20°-30°	148.5	31.9
30°-40°	89.8	19.3
40°-50°	31.4	6.8
50°-60°	8.0	1.7
60°-70°	3.1	0.7
70°-80°	1.0	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	331.5	71.3
0°-40°	421.2	90.6
0°-60°	460.7	99.1
0°-90°	465.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	465.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	560	
5°	550	52
15°	471	131
25°	330	149
35°	141	90
45°	38	31
55°	8	8
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P858923

CATALOG NUMBER: LX4C05D010 EX4C059030 4LBMDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	560.2
2.5°	557.9
5°	550.5
7.5°	537.5
10°	518.7
12.5°	496.0
15°	470.8
17.5°	443.1
20°	412.3
22.5°	374.5
25°	330.3
27.5°	279.7
30°	229.5
32.5°	181.4
35°	140.7
37.5°	106.7
40°	79.6
42.5°	57.2
45°	37.9
47.5°	23.3
50°	15.6
52.5°	11.2
55°	8.4
57.5°	6.4
60°	4.9
62.5°	3.9
65°	3.0
67.5°	2.3
70°	1.8
72.5°	1.3
75°	0.9
77.5°	0.6
80°	0.4
82.5°	0.3
85°	0.1
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)