

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858924

Luminaire Tested: **LX4C05D010 EX4C059030 4LBMDLI**

Issue Date: 2/18/2022



Test Information

Test Method: LM-79-08
Report Number: P858924
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-8)
Test Lab: INNOVATION CENTER
Issue Date: 2/18/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C05D010 EX4C059030 4LBMDLI
Description: 4 INCH 500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS AND 4LRMD45 TRIM WITH LI FINISH, DIM TO WARM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 540.0 lumens
Efficiency: N/A
Efficacy: 75.0 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.82
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858924

CATALOG NUMBER: LX4C05D010 EX4C059030 4LBMDLI

Luminous Intensity Polar Plot





TEST NUMBER: P858924

CATALOG NUMBER: LX4C05D010 EX4C059030 4LBMDLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			94
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88			88
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83			83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78			78
5	94	87	81	77	93	86	81	77	84	79	76	82	78	75	81	77	75	73			73
6	90	82	76	72	89	81	76	72	79	75	71	78	74	71	77	73	70	69			69
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65			65
8	82	73	68	64	81	73	67	64	72	67	63	71	66	63	70	66	63	62			62
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	66	63	60	58			58
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	63	59	57	55			55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	87140
5°	90100
10°	91017
15°	81985
20°	68141
25°	53449
30°	39125
35°	20217
40°	9606
45°	3371
50°	765
55°	493
60°	344
65°	262
70°	180
75°	142
80°	71
85°	0



TEST NUMBER: P858924

CATALOG NUMBER: LX4C05D010 EX4C059030 4LBMDLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.8	12.9
10°-20°	177.6	32.9
20°-30°	179.7	33.3
30°-40°	91.6	17.0
40°-50°	18.0	3.3
50°-60°	2.2	0.4
60°-70°	0.9	0.2
70°-80°	0.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	427.0	79.1
0°-40°	518.6	96.0
0°-60°	538.7	99.8
0°-90°	540.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	540.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	709	
5°	731	70
15°	645	178
25°	394	180
35°	135	92
45°	19	18
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P858924

CATALOG NUMBER: LX4C05D010 EX4C059030 4LBMDLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	709.3
2.5°	715.8
5°	730.6
7.5°	739.1
10°	729.6
12.5°	697.5
15°	644.6
17.5°	582.2
20°	521.2
22.5°	457.9
25°	394.3
27.5°	331.0
30°	275.8
32.5°	207.8
35°	134.8
37.5°	90.2
40°	59.9
42.5°	37.6
45°	19.4
47.5°	7.0
50°	4.0
52.5°	3.0
55°	2.3
57.5°	1.8
60°	1.4
62.5°	1.2
65°	0.9
67.5°	0.6
70°	0.5
72.5°	0.4
75°	0.3
77.5°	0.3
80°	0.1
82.5°	0.1
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)