

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859607

Luminaire Tested: **LX4C75D010 EX4C759050 4LBWH**

Issue Date: 2/8/2022

**Test Information**

Test Method: LM-79-08  
Report Number: P859607  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/8/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX4C75D010 EX4C759050 4LBWH  
Description: 4 INCH 7500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS  
AND 4LBW TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver:


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7137.0 lumens  
Efficiency: N/A  
Efficacy: 87.6 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 81.5  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P859607

CATALOG NUMBER: LX4C75D010 EX4C759050 4LBWH

### Luminous Intensity Polar Plot





TEST NUMBER: P859607

CATALOG NUMBER: LX4C75D010 EX4C759050 4LBWH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91																			
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82																			
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74																			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67																			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61																			
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55																			
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50																			
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46																			
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43																			
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	565151
5°	567309
10°	569029
15°	569061
20°	565938
25°	552680
30°	516565
35°	447335
40°	349439
45°	250726
50°	162878
55°	97499
60°	57053
65°	36628
70°	24390
75°	18417
80°	13725
85°	0



TEST NUMBER: P859607

CATALOG NUMBER: LX4C75D010 EX4C759050 4LBWH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	438.1	6.1
10°-20°	1262.3	17.7
20°-30°	1862.7	26.1
30°-40°	1838.2	25.8
40°-50°	1124.9	15.8
50°-60°	431.3	6.0
60°-70°	134.8	1.9
70°-80°	39.6	0.6
80°-90°	5.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3563.1	49.9
0°-40°	5401.2	75.7
0°-60°	6957.4	97.5
0°-90°	7137.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7137.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4600	
5°	4600	438
15°	4474	1262
25°	4077	1863
35°	2983	1838
45°	1443	1125
55°	455	431
65°	126	135
75°	39	40
85°	0	5
90°	0	



TEST NUMBER: P859607

CATALOG NUMBER: LX4C75D010 EX4C759050 4LBWH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4600.2
2.5°	4609.9
5°	4600.2
7.5°	4590.5
10°	4561.4
12.5°	4522.7
15°	4474.2
17.5°	4416.0
20°	4328.8
22.5°	4232.3
25°	4077.2
27.5°	3883.3
30°	3641.4
32.5°	3341.3
35°	2982.7
37.5°	2585.6
40°	2178.9
42.5°	1801.3
45°	1443.1
47.5°	1123.2
50°	852.2
52.5°	629.7
55°	455.2
57.5°	319.5
60°	232.2
62.5°	174.5
65°	126.0
67.5°	96.9
70°	67.9
72.5°	48.5
75°	38.8
77.5°	19.4
80°	19.4
82.5°	9.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)