

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858957

Luminaire Tested: **LX4C50D010 EX4C509027 4LBMDLI**

Issue Date: 2/18/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P858957  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/18/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX4C50D010 EX4C509027 4LBMDLI  
Description: 4 INCH 5000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS  
AND 4LRMD45 TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4194.0 lumens  
Efficiency: N/A  
Efficacy: 71.8 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.82  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 58.4  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P858957

CATALOG NUMBER: LX4C50D010 EX4C509027 4LBMDLI

### Luminous Intensity Polar Plot





TEST NUMBER: P858957

CATALOG NUMBER: LX4C50D010 EX4C509027 4LBMDLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |    |    |   |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |    | 0  |   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |   |
| 1   | 114 | 111 | 109 | 107 | 111 | 109 | 107 | 105 | 105 | 103 | 102 | 101 | 100 | 99  | 98  | 97  | 96  | 94  |    |    |   |
| 2   | 109 | 104 | 100 | 97  | 107 | 102 | 99  | 96  | 99  | 96  | 94  | 96  | 94  | 92  | 94  | 92  | 90  | 88  |    |    |   |
| 3   | 104 | 98  | 93  | 89  | 102 | 96  | 92  | 89  | 94  | 90  | 87  | 91  | 88  | 86  | 89  | 87  | 85  | 83  |    |    |   |
| 4   | 99  | 92  | 87  | 83  | 97  | 91  | 86  | 82  | 89  | 85  | 81  | 87  | 83  | 80  | 85  | 82  | 79  | 78  |    |    |   |
| 5   | 94  | 87  | 81  | 77  | 93  | 86  | 81  | 77  | 84  | 79  | 76  | 82  | 78  | 75  | 81  | 77  | 75  | 73  |    |    |   |
| 6   | 90  | 82  | 76  | 72  | 89  | 81  | 76  | 72  | 80  | 75  | 71  | 78  | 74  | 71  | 77  | 73  | 70  | 69  |    |    |   |
| 7   | 86  | 77  | 72  | 68  | 85  | 77  | 71  | 68  | 75  | 71  | 67  | 74  | 70  | 67  | 73  | 69  | 67  | 65  |    |    |   |
| 8   | 82  | 73  | 68  | 64  | 81  | 73  | 67  | 64  | 72  | 67  | 63  | 71  | 66  | 63  | 70  | 66  | 63  | 62  |    |    |   |
| 9   | 79  | 70  | 64  | 60  | 78  | 69  | 64  | 60  | 68  | 63  | 60  | 67  | 63  | 60  | 66  | 63  | 60  | 58  |    |    |   |
| 10  | 75  | 66  | 61  | 57  | 74  | 66  | 61  | 57  | 65  | 60  | 57  | 64  | 60  | 57  | 63  | 59  | 57  | 55  |    |    |   |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 676738 |
| 5°  | 699795 |
| 10° | 706888 |
| 15° | 636776 |
| 20° | 529175 |
| 25° | 415161 |
| 30° | 303834 |
| 35° | 157010 |
| 40° | 74574  |
| 45° | 26235  |
| 50° | 5925   |
| 55° | 3855   |
| 60° | 2703   |
| 65° | 2035   |
| 70° | 1437   |
| 75° | 949    |
| 80° | 707    |
| 85° | 0      |



TEST NUMBER: P858957

CATALOG NUMBER: LX4C50D010 EX4C509027 4LBMDLI

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 542.0  | 12.9      |
| 10°-20°   | 1379.0 | 32.9      |
| 20°-30°   | 1395.4 | 33.3      |
| 30°-40°   | 711.4  | 17.0      |
| 40°-50°   | 139.5  | 3.3       |
| 50°-60°   | 16.9   | 0.4       |
| 60°-70°   | 7.0    | 0.2       |
| 70°-80°   | 2.5    | 0.1       |
| 80°-90°   | 0.4    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 3316.4 | 79.1      |
| 0°-40°    | 4027.7 | 96.0      |
| 0°-60°    | 4184.1 | 99.8      |
| 0°-90°    | 4194.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 4194.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 5508 |      |
| 5°  | 5674 | 542  |
| 15° | 5007 | 1379 |
| 25° | 3063 | 1395 |
| 35° | 1047 | 711  |
| 45° | 151  | 139  |
| 55° | 18   | 17   |
| 65° | 7    | 7    |
| 75° | 2    | 3    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P858957

CATALOG NUMBER: LX4C50D010 EX4C509027 4LBMDLI

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 5508.5 |
| 2.5°  | 5559.5 |
| 5°    | 5674.5 |
| 7.5°  | 5740.5 |
| 10°   | 5666.5 |
| 12.5° | 5417.5 |
| 15°   | 5006.6 |
| 17.5° | 4521.6 |
| 20°   | 4047.6 |
| 22.5° | 3556.7 |
| 25°   | 3062.7 |
| 27.5° | 2570.8 |
| 30°   | 2141.8 |
| 32.5° | 1613.9 |
| 35°   | 1046.9 |
| 37.5° | 700.9  |
| 40°   | 465.0  |
| 42.5° | 292.0  |
| 45°   | 151.0  |
| 47.5° | 54.0   |
| 50°   | 31.0   |
| 52.5° | 23.0   |
| 55°   | 18.0   |
| 57.5° | 14.0   |
| 60°   | 11.0   |
| 62.5° | 9.0    |
| 65°   | 7.0    |
| 67.5° | 5.0    |
| 70°   | 4.0    |
| 72.5° | 3.0    |
| 75°   | 2.0    |
| 77.5° | 2.0    |
| 80°   | 1.0    |
| 82.5° | 1.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)