

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859608

Luminaire Tested: **LX4C75D010 EX4C759050 4LBWLI**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P859608
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C75D010 EX4C759050 4LBWLI
Description: 4 INCH 7500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS
AND 4LBW TRIM WITH LI FINISH
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8454.0 lumens
Efficiency: N/A
Efficacy: 103.7 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 81.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859608

CATALOG NUMBER: LX4C75D010 EX4C759050 4LBWLI

Luminous Intensity Polar Plot





TEST NUMBER: P859608

CATALOG NUMBER: LX4C75D010 EX4C759050 4LBWLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1 | 113 | 110 | 107 | 105 | 110 | 108 | 105 | 103 | 104 | 102 | 100 | 100 | 98 | 97 | 96 | 95 | 94 | 92 | 92 | 92 | 92 |
| 2 | 106 | 101 | 97 | 93 | 104 | 99 | 95 | 92 | 96 | 93 | 90 | 93 | 90 | 88 | 90 | 88 | 86 | 84 | 84 | 84 | 84 |
| 3 | 100 | 93 | 87 | 83 | 98 | 92 | 86 | 82 | 89 | 85 | 81 | 86 | 83 | 80 | 84 | 81 | 78 | 77 | 77 | 77 | 77 |
| 4 | 94 | 86 | 79 | 75 | 92 | 84 | 79 | 74 | 82 | 77 | 73 | 80 | 76 | 72 | 78 | 75 | 72 | 70 | 70 | 70 | 70 |
| 5 | 88 | 79 | 72 | 68 | 87 | 78 | 72 | 67 | 76 | 71 | 67 | 74 | 70 | 66 | 73 | 69 | 65 | 64 | 64 | 64 | 64 |
| 6 | 83 | 73 | 66 | 62 | 82 | 72 | 66 | 61 | 71 | 65 | 61 | 69 | 64 | 60 | 68 | 63 | 60 | 58 | 58 | 58 | 58 |
| 7 | 78 | 68 | 61 | 56 | 77 | 67 | 61 | 56 | 66 | 60 | 56 | 64 | 59 | 55 | 63 | 59 | 55 | 54 | 54 | 54 | 54 |
| 8 | 74 | 63 | 56 | 52 | 72 | 62 | 56 | 51 | 61 | 55 | 51 | 60 | 55 | 51 | 59 | 54 | 51 | 49 | 49 | 49 | 49 |
| 9 | 69 | 59 | 52 | 48 | 68 | 58 | 52 | 47 | 57 | 51 | 47 | 56 | 51 | 47 | 55 | 50 | 47 | 45 | 45 | 45 | 45 |
| 10 | 66 | 55 | 48 | 44 | 65 | 54 | 48 | 44 | 53 | 48 | 44 | 53 | 47 | 44 | 52 | 47 | 43 | 42 | 42 | 42 | 42 |

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P859608

CATALOG NUMBER: LX4C75D010 EX4C759050 4LBWLI

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 506.5 | 6.0 |
| 10°-20° | 1598.6 | 18.9 |
| 20°-30° | 2493.8 | 29.5 |
| 30°-40° | 2426.4 | 28.7 |
| 40°-50° | 1212.0 | 14.3 |
| 50°-60° | 187.7 | 2.2 |
| 60°-70° | 22.7 | 0.3 |
| 70°-80° | 6.4 | 0.1 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 4598.9 | 54.4 |
| 0°-40° | 7025.4 | 83.1 |
| 0°-60° | 8425.0 | 99.7 |
| 0°-90° | 8454.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 8454.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 5180 | |
| 5° | 5248 | 507 |
| 15° | 5645 | 1599 |
| 25° | 5480 | 2494 |
| 35° | 3941 | 2426 |
| 45° | 1520 | 1212 |
| 55° | 155 | 188 |
| 65° | 19 | 23 |
| 75° | 10 | 6 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P859608

CATALOG NUMBER: LX4C75D010 EX4C759050 4LBWLI

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 5179.7 |
| 2.5° | 5199.1 |
| 5° | 5247.6 |
| 7.5° | 5325.1 |
| 10° | 5422.1 |
| 12.5° | 5547.7 |
| 15° | 5644.6 |
| 17.5° | 5722.1 |
| 20° | 5731.8 |
| 22.5° | 5664.0 |
| 25° | 5480.2 |
| 27.5° | 5208.8 |
| 30° | 4870.0 |
| 32.5° | 4444.3 |
| 35° | 3940.6 |
| 37.5° | 3388.5 |
| 40° | 2807.8 |
| 42.5° | 2188.2 |
| 45° | 1520.2 |
| 47.5° | 977.8 |
| 50° | 590.5 |
| 52.5° | 319.5 |
| 55° | 155.1 |
| 57.5° | 67.9 |
| 60° | 38.8 |
| 62.5° | 29.1 |
| 65° | 19.4 |
| 67.5° | 19.4 |
| 70° | 9.7 |
| 72.5° | 9.7 |
| 75° | 9.7 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)