

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858983

Luminaire Tested: **LX4C50D010 EX4C509030 4LBSH**

Issue Date: 2/14/2022

Test Information

Test Method: LM-79-08
Report Number: P858983
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)
Test Lab: INNOVATION CENTER
Issue Date: 2/14/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C50D010 EX4C509030 4LBSH
Description: 4 INCH 5000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBS TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5183.0 lumens
Efficiency: N/A
Efficacy: 88.7 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 58.4
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858983

CATALOG NUMBER: LX4C50D010 EX4C509030 4LBSH

Luminous Intensity Polar Plot





TEST NUMBER: P858983

CATALOG NUMBER: LX4C50D010 EX4C509030 4LBSH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	333019
5°	331479
10°	324634
15°	312830
20°	298435
25°	282345
30°	266340
35°	250761
40°	236118
45°	220113
50°	200701
55°	177241
60°	150029
65°	117790
70°	84053
75°	46043
80°	8136
85°	0



TEST NUMBER: P858983

CATALOG NUMBER: LX4C50D010 EX4C509030 4LBSH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	253.9	4.9
10°-20°	690.1	13.3
20°-30°	958.4	18.5
30°-40°	1045.8	20.2
40°-50°	975.6	18.8
50°-60°	740.5	14.3
60°-70°	405.5	7.8
70°-80°	111.6	2.2
80°-90°	1.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1902.4	36.7
0°-40°	2948.3	56.9
0°-60°	4664.4	90.0
0°-90°	5183.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5183.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2711	
5°	2688	254
15°	2460	690
25°	2083	958
35°	1672	1046
45°	1267	976
55°	828	741
65°	405	405
75°	97	112
85°	0	2
90°	0	



TEST NUMBER: P858983

CATALOG NUMBER: LX4C50D010 EX4C509030 4LBSH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2710.7
2.5°	2710.7
5°	2687.9
7.5°	2653.7
10°	2602.3
12.5°	2533.9
15°	2459.6
17.5°	2368.4
20°	2282.7
22.5°	2180.0
25°	2082.9
27.5°	1986.0
30°	1877.5
32.5°	1774.8
35°	1672.0
37.5°	1569.3
40°	1472.3
42.5°	1369.6
45°	1266.9
47.5°	1164.1
50°	1050.1
52.5°	941.6
55°	827.5
57.5°	719.0
60°	610.6
62.5°	502.2
65°	405.2
67.5°	313.8
70°	234.0
72.5°	159.8
75°	97.0
77.5°	45.6
80°	11.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)