

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859024

Luminaire Tested: **LX4C50D010 EX4C509040 4LBNI**

Issue Date: 1/21/2022

**Test Information**

Test Method: LM-79-08  
Report Number: P859024  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/21/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX4C50D010 EX4C509040 4LBNLI  
Description: 4 INCH 5000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS  
AND 4LBN TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver:


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3945.1 lumens  
Efficiency: N/A  
Efficacy: 67.6 lumens/watt  
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 58.4  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P859024

CATALOG NUMBER: LX4C50D010 EX4C509040 4LBNLI

### Luminous Intensity Polar Plot





TEST NUMBER: P859024

CATALOG NUMBER: LX4C50D010 EX4C509040 4LBNLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	92	90	90	90	90
3	105	99	95	92	103	98	94	91	95	92	89	93	90	88	91	89	87	85	85	85	85
4	101	94	89	86	99	93	88	85	91	87	84	89	86	83	87	84	82	81	81	81	81
5	96	89	84	80	95	88	84	80	87	82	79	85	81	79	83	80	78	77	77	77	77
6	92	85	80	76	91	84	79	76	83	78	75	81	78	75	80	77	74	73	73	73	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	69	69	69	69
8	85	77	72	68	84	77	72	68	76	71	68	75	71	68	74	70	67	66	66	66	66
9	82	74	69	65	81	73	68	65	72	68	65	72	68	65	71	67	64	63	63	63	63
10	79	71	66	62	78	70	65	62	69	65	62	69	65	62	68	64	62	61	61	61	61

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1247233
5°	1122373
10°	870085
15°	629768
20°	436063
25°	317901
30°	230989
35°	136688
40°	57494
45°	17930
50°	2332
55°	1307
60°	1499
65°	1773
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P859024

CATALOG NUMBER: LX4C50D010 EX4C509040 4LBNLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	800.1	20.3
10°-20°	1369.7	34.7
20°-30°	1088.6	27.6
30°-40°	576.3	14.6
40°-50°	99.3	2.5
50°-60°	7.5	0.2
60°-70°	3.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3258.3	82.6
0°-40°	3834.6	97.2
0°-60°	3941.3	99.9
0°-90°	3945.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3945.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	10152	
5°	9101	800
15°	4952	1370
25°	2345	1089
35°	911	576
45°	103	99
55°	6	7
65°	6	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P859024

CATALOG NUMBER: LX4C50D010 EX4C509040 4LBNLI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	10152.2
2.5°	9890.8
5°	9101.1
7.5°	8068.4
10°	6974.7
12.5°	5917.6
15°	4951.5
17.5°	4052.3
20°	3335.4
22.5°	2788.6
25°	2345.2
27.5°	1986.7
30°	1628.3
32.5°	1263.7
35°	911.4
37.5°	601.6
40°	358.5
42.5°	206.6
45°	103.2
47.5°	36.5
50°	12.2
52.5°	12.2
55°	6.1
57.5°	6.1
60°	6.1
62.5°	6.1
65°	6.1
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)