

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859046

Luminaire Tested: **LX4C50D010 EX4C509050 4LBSH**

Issue Date: 2/14/2022



Test Information

Test Method: LM-79-08
Report Number: P859046
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)
Test Lab: INNOVATION CENTER
Issue Date: 2/14/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C50D010 EX4C509050 4LBSH
Description: 4 INCH 5000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS
AND 4LBS TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5372.0 lumens
Efficiency: N/A
Efficacy: 92.0 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 58.4
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859046

CATALOG NUMBER: LX4C50D010 EX4C509050 4LBSH

Luminous Intensity Polar Plot





TEST NUMBER: P859046

CATALOG NUMBER: LX4C50D010 EX4C509050 4LBSH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	345157
5°	343565
10°	336472
15°	324239
20°	309313
25°	292647
30°	276043
35°	259909
40°	244730
45°	228139
50°	208022
55°	183709
60°	155508
65°	122092
70°	87142
75°	47752
80°	8419
85°	0



TEST NUMBER: P859046

CATALOG NUMBER: LX4C50D010 EX4C509050 4LBSH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	263.2	4.9
10°-20°	715.3	13.3
20°-30°	993.3	18.5
30°-40°	1084.0	20.2
40°-50°	1011.2	18.8
50°-60°	767.5	14.3
60°-70°	420.3	7.8
70°-80°	115.7	2.2
80°-90°	1.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1971.8	36.7
0°-40°	3055.8	56.9
0°-60°	4834.5	90.0
0°-90°	5372.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5372.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2810	
5°	2786	263
15°	2549	715
25°	2159	993
35°	1733	1084
45°	1313	1011
55°	858	768
65°	420	420
75°	101	116
85°	0	2
90°	0	



TEST NUMBER: P859046

CATALOG NUMBER: LX4C50D010 EX4C509050 4LBSH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2809.5
2.5°	2809.5
5°	2785.9
7.5°	2750.5
10°	2697.2
12.5°	2626.3
15°	2549.3
17.5°	2454.7
20°	2365.9
22.5°	2259.4
25°	2158.9
27.5°	2058.4
30°	1945.9
32.5°	1839.5
35°	1733.0
37.5°	1626.6
40°	1526.0
42.5°	1419.5
45°	1313.1
47.5°	1206.6
50°	1088.4
52.5°	975.9
55°	857.7
57.5°	745.2
60°	632.9
62.5°	520.5
65°	420.0
67.5°	325.3
70°	242.6
72.5°	165.6
75°	100.6
77.5°	47.3
80°	11.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)