

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859203

Luminaire Tested: **LX4C60D010 EX4C609030 4LBSH**

Issue Date: 2/14/2022

Test Information

Test Method: LM-79-08
Report Number: P859203
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205729)
Test Lab: INNOVATION CENTER
Issue Date: 2/14/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C60D010 EX4C609030 4LBSH
Description: 4 INCH 6000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBS TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6264.0 lumens
Efficiency: N/A
Efficacy: 87.0 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 72
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859203

CATALOG NUMBER: LX4C60D010 EX4C609030 4LBSH

Luminous Intensity Polar Plot





TEST NUMBER: P859203

CATALOG NUMBER: LX4C60D010 EX4C609030 4LBSH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77																			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67																			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58																			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51																			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46																			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41																			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37																			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34																			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	402468
5°	400614
10°	392335
15°	378077
20°	360680
25°	341230
30°	321892
35°	303072
40°	285369
45°	266015
50°	242558
55°	214210
60°	181332
65°	142354
70°	101618
75°	55679
80°	9834
85°	0



TEST NUMBER: P859203

CATALOG NUMBER: LX4C60D010 EX4C609030 4LSH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	306.9	4.9
10°-20°	834.1	13.3
20°-30°	1158.3	18.5
30°-40°	1264.0	20.2
40°-50°	1179.1	18.8
50°-60°	895.0	14.3
60°-70°	490.1	7.8
70°-80°	134.9	2.2
80°-90°	1.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2299.2	36.7
0°-40°	3563.2	56.9
0°-60°	5637.2	90.0
0°-90°	6264.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6264.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3276	
5°	3248	307
15°	2973	834
25°	2517	1158
35°	2021	1264
45°	1531	1179
55°	1000	895
65°	490	490
75°	117	135
85°	0	2
90°	0	



TEST NUMBER: P859203

CATALOG NUMBER: LX4C60D010 EX4C609030 4LBSH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3276.0
2.5°	3276.0
5°	3248.5
7.5°	3207.2
10°	3145.0
12.5°	3062.3
15°	2972.6
17.5°	2862.3
20°	2758.8
22.5°	2634.6
25°	2517.3
27.5°	2400.2
30°	2269.1
32.5°	2144.9
35°	2020.8
37.5°	1896.6
40°	1779.4
42.5°	1655.2
45°	1531.1
47.5°	1406.9
50°	1269.1
52.5°	1138.0
55°	1000.1
57.5°	869.0
60°	738.0
62.5°	607.0
65°	489.7
67.5°	379.3
70°	282.9
72.5°	193.1
75°	117.3
77.5°	55.1
80°	13.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)