

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859236

Luminaire Tested: **LD4C60D010 EU4609040 4LBMLI**

Issue Date: 7/19/2024

Test Information

Test Method: LM-79-08
Report Number: P859236
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208178)
Test Lab: INNOVATION CENTER
Issue Date: 7/19/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C60D010 EU4609040 4LBMLI
Description: 4 INCH 6000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 4LBM TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6077.0 lumens
Efficiency: N/A
Efficacy: 84.4 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 72
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859236

CATALOG NUMBER: LD4C60D010 EU4609040 4LBMLI

Luminous Intensity Polar Plot





TEST NUMBER: P859236

CATALOG NUMBER: LD4C60D010 EU4609040 4LBMLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88			
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83			
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78			
5	94	87	81	77	93	86	81	77	84	79	76	82	78	75	81	77	75	73			
6	90	82	76	72	89	81	76	72	80	75	71	78	74	71	77	73	71	69			
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65			
8	82	73	68	64	81	73	67	64	72	67	64	71	66	63	70	66	63	62			
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	67	63	60	58			
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	64	60	57	56			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1176936
5°	1156940
10°	1063033
15°	890235
20°	713228
25°	573067
30°	426598
35°	243712
40°	114379
45°	48561
50°	15462
55°	7882
60°	5430
65°	4273
70°	2658
75°	0
80°	0
85°	0



TEST NUMBER: P859236

CATALOG NUMBER: LD4C60D010 EU4609040 4LBMLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	867.4	14.3
10°-20°	1939.2	31.9
20°-30°	1928.0	31.7
30°-40°	1050.0	17.3
40°-50°	242.7	4.0
50°-60°	34.2	0.6
60°-70°	12.7	0.2
70°-80°	2.9	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4734.6	77.9
0°-40°	5784.6	95.2
0°-60°	6061.5	99.7
0°-90°	6077.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6077.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9580	
5°	9381	867
15°	6999	1939
25°	4228	1928
35°	1625	1050
45°	280	243
55°	37	34
65°	15	13
75°	0	3
85°	0	0
90°	0	



TEST NUMBER: P859236

CATALOG NUMBER: LD4C60D010 EU4609040 4LBMLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	9580.0
2.5°	9557.9
5°	9381.4
7.5°	9021.3
10°	8521.4
12.5°	7786.2
15°	6999.4
17.5°	6220.0
20°	5455.4
22.5°	4830.5
25°	4227.6
27.5°	3654.2
30°	3007.2
32.5°	2286.7
35°	1625.0
37.5°	1095.4
40°	713.2
42.5°	448.4
45°	279.5
47.5°	161.8
50°	80.9
52.5°	44.1
55°	36.8
57.5°	22.1
60°	22.1
62.5°	14.7
65°	14.7
67.5°	7.4
70°	7.4
72.5°	7.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)