

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859263

Luminaire Tested: **LX4C60D010 EX4C609050 4LBMLI**

Issue Date: 1/26/2022



Test Information

Test Method: LM-79-08
Report Number: P859263
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER
Issue Date: 1/26/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C60D010 EX4C609050 4LBMLI
Description: 4 INCH 6000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS
AND 4LBM TRIM WITH LI FINISH
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6202.0 lumens
Efficiency: N/A
Efficacy: 86.1 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 72
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859263

CATALOG NUMBER: LX4C60D010 EX4C609050 4LBMLI

Luminous Intensity Polar Plot





TEST NUMBER: P859263

CATALOG NUMBER: LX4C60D010 EX4C609050 4LBMLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	92	90	90	90	90
3	105	99	95	92	103	98	94	91	95	92	89	93	90	88	91	89	87	85	85	85	85
4	101	94	89	86	99	93	88	85	91	87	84	89	86	83	87	84	82	81	81	81	81
5	96	89	84	80	95	88	84	80	87	82	79	85	81	79	83	80	78	77	77	77	77
6	92	85	80	76	91	84	79	76	83	78	75	81	78	75	80	77	74	73	73	73	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	69	69	69	69
8	85	77	72	68	84	77	72	68	76	71	68	75	71	68	74	70	67	66	66	66	66
9	82	74	69	65	81	73	68	65	72	68	65	72	68	65	71	67	64	63	63	63	63
10	79	71	66	62	78	70	65	62	69	65	62	69	65	62	68	64	62	61	61	61	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1960791
5°	1764502
10°	1367882
15°	990064
20°	685537
25°	499773
30°	363131
35°	214886
40°	90371
45°	28181
50°	3651
55°	2056
60°	2359
65°	2791
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P859263

CATALOG NUMBER: LX4C60D010 EX4C609050 4LBMLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1257.8	20.3
10°-20°	2153.3	34.7
20°-30°	1711.4	27.6
30°-40°	906.0	14.6
40°-50°	156.1	2.5
50°-60°	11.7	0.2
60°-70°	5.9	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5122.4	82.6
0°-40°	6028.4	97.2
0°-60°	6196.2	99.9
0°-90°	6202.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6202.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	15960	
5°	14308	###
15°	7784	2153
25°	3687	1711
35°	1433	906
45°	162	156
55°	10	12
65°	10	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P859263

CATALOG NUMBER: LX4C60D010 EX4C609050 4LBMLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	15960.4
2.5°	15549.5
5°	14308.0
7.5°	12684.4
10°	10965.1
12.5°	9303.2
15°	7784.3
17.5°	6370.7
20°	5243.6
22.5°	4383.9
25°	3686.9
27.5°	3123.4
30°	2559.8
32.5°	1986.7
35°	1432.8
37.5°	945.8
40°	563.5
42.5°	324.8
45°	162.2
47.5°	57.4
50°	19.1
52.5°	19.1
55°	9.6
57.5°	9.6
60°	9.6
62.5°	9.6
65°	9.6
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)