

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859264

Luminaire Tested: **LX4C60D010 EX4C609050 4LBNH**

Issue Date: 2/8/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P859264  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/8/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX4C60D010 EX4C609050 4LBNH  
Description: 4 INCH 6000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS  
AND 4LBN TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver:

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4129.9 lumens  
Efficiency: N/A  
Efficacy: 57.4 lumens/watt  
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 72  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P859264

CATALOG NUMBER: LX4C60D010 EX4C609050 4LBNH

### Luminous Intensity Polar Plot





TEST NUMBER: P859264

CATALOG NUMBER: LX4C60D010 EX4C609050 4LBNH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	74	65	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	637044
5°	622866
10°	575902
15°	516762
20°	454890
25°	391479
30°	315253
35°	209862
40°	109166
45°	49412
50°	21444
55°	14393
60°	9214
65°	6541
70°	5388
75°	3560
80°	0
85°	0



TEST NUMBER: P859264

CATALOG NUMBER: LX4C60D010 EX4C609050 4LBNH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	467.8	11.3
10°-20°	1134.8	27.5
20°-30°	1317.5	31.9
30°-40°	872.5	21.1
40°-50°	244.7	5.9
50°-60°	61.5	1.5
60°-70°	23.1	0.6
70°-80°	7.9	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2920.2	70.7
0°-40°	3792.7	91.8
0°-60°	4098.9	99.2
0°-90°	4129.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4129.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5185	
5°	5051	468
15°	4063	1135
25°	2888	1318
35°	1399	873
45°	284	245
55°	67	61
65°	22	23
75°	8	8
85°	0	0
90°	0	



TEST NUMBER: P859264

CATALOG NUMBER: LX4C60D010 EX4C609050 4LBNH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5185.4
2.5°	5162.9
5°	5050.7
7.5°	4855.9
10°	4616.5
12.5°	4347.1
15°	4063.0
17.5°	3786.0
20°	3479.4
22.5°	3195.0
25°	2888.0
27.5°	2596.4
30°	2222.3
32.5°	1825.7
35°	1399.3
37.5°	1002.7
40°	680.7
42.5°	441.3
45°	284.4
47.5°	172.2
50°	112.2
52.5°	82.2
55°	67.2
57.5°	52.5
60°	37.5
62.5°	30.0
65°	22.5
67.5°	15.0
70°	15.0
72.5°	7.5
75°	7.5
77.5°	7.5
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)