

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P#

Luminaire Tested: **LD4C40D010 EX4C409027 4LBSQH**

Issue Date: 2/9/2022



Test Information

Test Method: LM-79-08
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER
Issue Date: 2/9/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C40D010 EX4C409027 4LBSQH
Description: 4 INCH 4000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS
AND 4LBSQ TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3082.0 lumens
Efficiency: N/A
Efficacy: 65.6 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P#
CATALOG NUMBER: LD4C40D010 EX4C409027 4LBSQH

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LD4C40D010 EX4C409027 4LBSQH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85	85	85	85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79	79	79	79
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73	73	73	73
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67	67	67	67
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62	62	62	62
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58	58	58	58
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54	54	54	54
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50	50	50	50
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47	47	47	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	294870
5°	290592
10°	278442
15°	262987
20°	245491
25°	222850
30°	186053
35°	134788
40°	84379
45°	48224
50°	25143
55°	14097
60°	8973
65°	5320
70°	3950
75°	1752
80°	2612
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LD4C40D010 EX4C409027 4LBSQH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	281.2	9.1
10°-20°	737.7	23.9
20°-30°	948.1	30.8
30°-40°	713.3	23.1
40°-50°	286.5	9.3
50°-60°	81.4	2.6
60°-70°	25.8	0.8
70°-80°	7.4	0.2
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1967.0	63.8
0°-40°	2680.3	87.0
0°-60°	3048.2	98.9
0°-90°	3082.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3082.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3056	
5°	3000	281
15°	2633	738
25°	2093	948
35°	1144	713
45°	353	286
55°	84	81
65°	23	26
75°	5	7
85°	0	1
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LD4C40D010 EX4C409027 4LBSQH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3056.0
2.5°	3037.4
5°	3000.2
7.5°	2930.4
10°	2841.9
12.5°	2735.1
15°	2632.7
17.5°	2516.4
20°	2390.8
22.5°	2256.0
25°	2093.2
27.5°	1897.7
30°	1669.9
32.5°	1414.0
35°	1144.3
37.5°	893.0
40°	669.9
42.5°	493.0
45°	353.4
47.5°	242.0
50°	167.5
52.5°	116.3
55°	83.8
57.5°	60.5
60°	46.5
62.5°	32.6
65°	23.3
67.5°	18.6
70°	14.0
72.5°	9.3
75°	4.7
77.5°	4.7
80°	4.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)