

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859316

Luminaire Tested: **LX4C60D010 EX4C609030 4LBWLI**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P859316
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C60D010 EX4C609030 4LBWLI
Description: 4 INCH 6000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBW TRIM WITH LI FINISH, DIM TO WARM
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7387.2 lumens
Efficiency: N/A
Efficacy: 75.8 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 97.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859316

CATALOG NUMBER: LX4C60D010 EX4C609030 4LBWLI

Luminous Intensity Polar Plot





TEST NUMBER: P859316

CATALOG NUMBER: LX4C60D010 EX4C609030 4LBWLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92		
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84		
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77		
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70		
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64		
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58		
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54		
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49		
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45		
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P859316

CATALOG NUMBER: LX4C60D010 EX4C609030 4LBWLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	442.6	6.0
10°-20°	1396.9	18.9
20°-30°	2179.1	29.5
30°-40°	2120.3	28.7
40°-50°	1059.0	14.3
50°-60°	164.0	2.2
60°-70°	19.8	0.3
70°-80°	5.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4018.6	54.4
0°-40°	6138.8	83.1
0°-60°	7361.8	99.7
0°-90°	7387.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7387.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4526	
5°	4585	443
15°	4932	1397
25°	4789	2179
35°	3443	2120
45°	1328	1059
55°	136	164
65°	17	20
75°	8	6
85°	0	0
90°	0	



TEST NUMBER: P859316

CATALOG NUMBER: LX4C60D010 EX4C609030 4LBWLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	4526.1
2.5°	4543.1
5°	4585.4
7.5°	4653.2
10°	4737.8
12.5°	4847.6
15°	4932.3
17.5°	5000.1
20°	5008.5
22.5°	4949.2
25°	4788.6
27.5°	4551.5
30°	4255.5
32.5°	3883.5
35°	3443.3
37.5°	2961.0
40°	2453.4
42.5°	1912.1
45°	1328.4
47.5°	854.4
50°	516.0
52.5°	279.1
55°	135.6
57.5°	59.3
60°	33.9
62.5°	25.4
65°	17.0
67.5°	17.0
70°	8.4
72.5°	8.4
75°	8.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)