

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859279

Luminaire Tested: **LD4C60D010 EU4609030 4LBNH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P859279
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C60D010 EU4609030 4LBNH
Description: 4 INCH 6000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBN TRIM WITH H FINISH, DIM TO WARM
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4582.7 lumens
Efficiency: N/A
Efficacy: 47.0 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 97.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859279

CATALOG NUMBER: LD4C60D010 EU4609030 4LBNH

Luminous Intensity Polar Plot





TEST NUMBER: P859279

CATALOG NUMBER: LD4C60D010 EU4609030 4LBNH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	74	65	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	706874
5°	691150
10°	639038
15°	573398
20°	504766
25°	434409
30°	349810
35°	232868
40°	121130
45°	54850
50°	23795
55°	15957
60°	10221
65°	7267
70°	5999
75°	3940
80°	0
85°	0



TEST NUMBER: P859279

CATALOG NUMBER: LD4C60D010 EU4609030 4LBNH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	519.1	11.3
10°-20°	1259.2	27.5
20°-30°	1462.0	31.9
30°-40°	968.2	21.1
40°-50°	271.6	5.9
50°-60°	68.2	1.5
60°-70°	25.7	0.6
70°-80°	8.8	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3240.4	70.7
0°-40°	4208.5	91.8
0°-60°	4548.3	99.2
0°-90°	4582.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4582.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5754	
5°	5604	519
15°	4508	1259
25°	3205	1462
35°	1553	968
45°	316	272
55°	74	68
65°	25	26
75°	8	9
85°	0	0
90°	0	



TEST NUMBER: P859279

CATALOG NUMBER: LD4C60D010 EU4609030 4LBNH

CANDELA DISTRIBUTION (FULL):

	0°
0°	5753.8
2.5°	5728.8
5°	5604.4
7.5°	5388.2
10°	5122.6
12.5°	4823.7
15°	4508.3
17.5°	4201.1
20°	3860.9
22.5°	3545.2
25°	3204.7
27.5°	2881.1
30°	2465.9
32.5°	2025.8
35°	1552.7
37.5°	1112.6
40°	755.3
42.5°	489.7
45°	315.7
47.5°	191.1
50°	124.5
52.5°	91.2
55°	74.5
57.5°	58.3
60°	41.6
62.5°	33.3
65°	25.0
67.5°	16.7
70°	16.7
72.5°	8.3
75°	8.3
77.5°	8.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)