

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859372

Luminaire Tested: **LX4C65D010 EX4C659035 4LBMLI**

Issue Date: 1/26/2022



Test Information

Test Method: LM-79-08
Report Number: P859372
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER
Issue Date: 1/26/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C65D010 EX4C659035 4LBMLI
Description: 4 INCH 6500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 4LBM TRIM WITH LI FINISH
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6347.0 lumens
Efficiency: N/A
Efficacy: 87.7 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859372

CATALOG NUMBER: LX4C65D010 EX4C659035 4LBMLI

Luminous Intensity Polar Plot





TEST NUMBER: P859372

CATALOG NUMBER: LX4C65D010 EX4C659035 4LBMLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			95																
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	92	90			90																
3	105	99	95	92	103	98	94	91	95	92	89	93	90	88	91	89	87	85			85																
4	101	94	89	86	99	93	88	85	91	87	84	89	86	83	87	84	82	81			81																
5	96	89	84	80	95	88	84	80	87	82	79	85	81	79	83	80	78	77			77																
6	92	85	80	76	91	84	79	76	83	78	75	81	78	75	80	77	74	73			73																
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	69			69																
8	85	77	72	68	84	77	72	68	76	71	68	75	71	68	74	70	67	66			66																
9	82	74	69	65	81	73	68	65	72	68	65	72	68	65	71	67	64	63			63																
10	79	71	66	62	78	70	65	62	69	65	62	69	65	62	68	64	62	61			61																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2006627
5°	1805766
10°	1399855
15°	1013212
20°	701566
25°	511458
30°	371628
35°	219910
40°	92488
45°	28841
50°	3746
55°	2099
60°	2408
65°	2849
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P859372

CATALOG NUMBER: LX4C65D010 EX4C659035 4LBMLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1287.2	20.3
10°-20°	2203.6	34.7
20°-30°	1751.4	27.6
30°-40°	927.1	14.6
40°-50°	159.7	2.5
50°-60°	12.0	0.2
60°-70°	6.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5242.2	82.6
0°-40°	6169.3	97.2
0°-60°	6341.0	99.9
0°-90°	6347.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6347.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	16334	
5°	14643	###
15°	7966	2204
25°	3773	1751
35°	1466	927
45°	166	160
55°	10	12
65°	10	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P859372

CATALOG NUMBER: LX4C65D010 EX4C659035 4LBMLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	16333.5
2.5°	15913.0
5°	14642.6
7.5°	12980.9
10°	11221.4
12.5°	9520.7
15°	7966.3
17.5°	6519.6
20°	5366.2
22.5°	4486.4
25°	3773.1
27.5°	3196.4
30°	2619.7
32.5°	2033.2
35°	1466.3
37.5°	967.9
40°	576.7
42.5°	332.4
45°	166.0
47.5°	58.7
50°	19.6
52.5°	19.6
55°	9.8
57.5°	9.8
60°	9.8
62.5°	9.8
65°	9.8
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)