

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859387

Luminaire Tested: **LD4C65D010 EU4659040 4LBMLI**

Issue Date: 7/19/2024



Test Information

Test Method: LM-79-08
Report Number: P859387
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208178)
Test Lab: INNOVATION CENTER
Issue Date: 7/19/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C65D010 EU4659040 4LBMLI
Description: 4 INCH 6500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 4LBM TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6356.1 lumens
Efficiency: N/A
Efficacy: 87.8 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859387

CATALOG NUMBER: LD4C65D010 EU4659040 4LBMLI

Luminous Intensity Polar Plot





TEST NUMBER: P859387

CATALOG NUMBER: LD4C65D010 EU4659040 4LBMLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88			
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83			
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78			
5	94	87	81	77	93	86	81	77	84	79	76	82	78	75	81	77	75	73			
6	90	82	76	72	89	81	76	72	80	75	71	78	74	71	77	73	71	69			
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65			
8	82	73	68	64	81	73	67	64	72	67	64	71	66	63	70	66	63	62			
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	67	63	60	58			
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	64	60	57	56			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1230967
5°	1210055
10°	1111848
15°	931113
20°	745965
25°	599378
30°	446189
35°	254900
40°	119623
45°	50802
50°	16169
55°	8246
60°	5676
65°	4477
70°	2766
75°	0
80°	0
85°	0



TEST NUMBER: P859387

CATALOG NUMBER: LD4C65D010 EU4659040 4LBMLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	907.2	14.3
10°-20°	2028.2	31.9
20°-30°	2016.5	31.7
30°-40°	1098.2	17.3
40°-50°	253.8	4.0
50°-60°	35.8	0.6
60°-70°	13.3	0.2
70°-80°	3.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4952.0	77.9
0°-40°	6050.1	95.2
0°-60°	6339.8	99.7
0°-90°	6356.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6356.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10020	
5°	9812	907
15°	7321	2028
25°	4422	2017
35°	1700	1098
45°	292	254
55°	38	36
65°	15	13
75°	0	3
85°	0	0
90°	0	



TEST NUMBER: P859387

CATALOG NUMBER: LD4C65D010 EU4659040 4LBMLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	10019.8
2.5°	9996.8
5°	9812.1
7.5°	9435.5
10°	8912.7
12.5°	8143.6
15°	7320.8
17.5°	6505.6
20°	5705.8
22.5°	5052.2
25°	4421.7
27.5°	3822.0
30°	3145.3
32.5°	2391.7
35°	1699.6
37.5°	1145.6
40°	745.9
42.5°	469.0
45°	292.4
47.5°	169.3
50°	84.6
52.5°	46.2
55°	38.5
57.5°	23.1
60°	23.1
62.5°	15.4
65°	15.4
67.5°	7.7
70°	7.7
72.5°	7.7
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)