

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859418

Luminaire Tested: **LX4C65D010 EX4C659050 4LBSLI**

Issue Date: 2/9/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P859418  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208407)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/9/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX4C65D010 EX4C659050 4LBSLI  
Description: 4 INCH 6500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS  
AND 4LBS TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7082.9 lumens  
Efficiency: N/A  
Efficacy: 97.8 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 72.4  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P859418

CATALOG NUMBER: LX4C65D010 EX4C659050 4LBSLI

### Luminous Intensity Polar Plot





TEST NUMBER: P859418

CATALOG NUMBER: LX4C65D010 EX4C659050 4LBSLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90																			
2	104	98	93	88	102	96	91	87	93	89	85	90	86	84	87	84	82	80																			
3	97	89	82	77	95	87	81	77	84	79	75	82	78	74	79	76	73	71																			
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63																			
5	84	73	66	61	82	72	65	60	70	64	60	69	63	59	67	62	59	57																			
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51																			
7	74	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46																			
8	69	57	50	45	68	57	50	45	55	49	45	54	49	44	53	48	44	42																			
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39																			
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	621331
5°	607254
10°	570264
15°	530549
20°	492058
25°	448548
30°	399333
35°	353959
40°	318134
45°	284727
50°	244259
55°	196497
60°	146417
65°	93459
70°	45044
75°	7452
80°	5518
85°	0



TEST NUMBER: P859418

CATALOG NUMBER: LX4C65D010 EX4C659050 4LBSLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	458.6	6.5
10°-20°	1169.6	16.5
20°-30°	1515.5	21.4
30°-40°	1485.0	21.0
40°-50°	1258.6	17.8
50°-60°	825.1	11.6
60°-70°	331.6	4.7
70°-80°	37.9	0.5
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3143.7	44.4
0°-40°	4628.6	65.3
0°-60°	6712.4	94.8
0°-90°	7082.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7082.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5058	
5°	4924	459
15°	4171	1170
25°	3309	1516
35°	2360	1485
45°	1639	1259
55°	917	825
65°	322	332
75°	16	38
85°	0	1
90°	0	



TEST NUMBER: P859418

CATALOG NUMBER: LX4C65D010 EX4C659050 4LBSLI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5057.5
2.5°	5018.2
5°	4924.1
7.5°	4767.3
10°	4571.3
12.5°	4359.6
15°	4171.4
17.5°	3967.7
20°	3763.7
22.5°	3544.2
25°	3309.0
27.5°	3065.8
30°	2815.0
32.5°	2579.8
35°	2360.1
37.5°	2179.9
40°	1983.7
42.5°	1811.3
45°	1638.8
47.5°	1458.4
50°	1278.0
52.5°	1097.8
55°	917.4
57.5°	752.7
60°	595.9
62.5°	454.7
65°	321.5
67.5°	211.7
70°	125.4
72.5°	54.8
75°	15.7
77.5°	7.8
80°	7.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)