

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859460

Luminaire Tested: **LX4C70D010 EX4C709030 4LBMDLI**

Issue Date: 2/18/2022



**Test Information**


Test Method: LM-79-08  
Report Number: P859460  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/18/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX4C70D010 EX4C709030 4LBMDLI  
Description: 4 INCH 7000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS  
AND 4LRMD45 TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5789.0 lumens  
Efficiency: N/A  
Efficacy: 74.2 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.82  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 78  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P859460  
CATALOG NUMBER: LX4C70D010 EX4C709030 4LBMDLI

### Luminous Intensity Polar Plot





TEST NUMBER: P859460

CATALOG NUMBER: LX4C70D010 EX4C709030 4LBMDLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88			
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83			
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78			
5	94	87	81	77	93	86	81	77	84	79	76	82	78	75	81	77	75	73			
6	90	82	76	72	89	81	76	72	80	75	71	78	74	71	77	73	70	69			
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65			
8	82	73	68	64	81	73	67	64	72	67	63	71	66	63	70	66	63	62			
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	66	63	60	58			
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	63	59	57	55			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	934104
5°	965925
10°	975722
15°	878940
20°	730433
25°	573054
30°	419392
35°	216731
40°	102928
45°	36208
50°	8180
55°	5312
60°	3735
65°	2820
70°	1976
75°	1329
80°	990
85°	0



TEST NUMBER: P859460

CATALOG NUMBER: LX4C70D010 EX4C709030 4LBMDLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	748.1	12.9
10°-20°	1903.4	32.9
20°-30°	1926.1	33.3
30°-40°	981.9	17.0
40°-50°	192.5	3.3
50°-60°	23.3	0.4
60°-70°	9.7	0.2
70°-80°	3.5	0.1
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4577.6	79.1
0°-40°	5559.5	96.0
0°-60°	5775.3	99.8
0°-90°	5789.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5789.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7603	
5°	7832	748
15°	6911	1903
25°	4228	1926
35°	1445	982
45°	208	192
55°	25	23
65°	10	10
75°	3	3
85°	0	1
90°	0	



TEST NUMBER: P859460

CATALOG NUMBER: LX4C70D010 EX4C709030 4LBMDLI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	7603.4
2.5°	7673.8
5°	7832.5
7.5°	7923.6
10°	7821.5
12.5°	7477.8
15°	6910.6
17.5°	6241.2
20°	5587.0
22.5°	4909.3
25°	4227.5
27.5°	3548.4
30°	2956.4
32.5°	2227.6
35°	1445.1
37.5°	967.5
40°	641.8
42.5°	403.0
45°	208.4
47.5°	74.5
50°	42.8
52.5°	31.7
55°	24.8
57.5°	19.3
60°	15.2
62.5°	12.4
65°	9.7
67.5°	6.9
70°	5.5
72.5°	4.1
75°	2.8
77.5°	2.8
80°	1.4
82.5°	1.4
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)