

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859489

Luminaire Tested: **LX4C70D010 EX4C709035 4LBWH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P859489
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C70D010 EX4C709035 4LBWH
Description: 4 INCH 7000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 4LBW TRIM WITH H FINISH
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5939.0 lumens
Efficiency: N/A
Efficacy: 76.1 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 78
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859489

CATALOG NUMBER: LX4C70D010 EX4C709035 4LBWH

Luminous Intensity Polar Plot





TEST NUMBER: P859489

CATALOG NUMBER: LX4C70D010 EX4C709035 4LBWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			91
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			82
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			67
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			61
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			55
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			50
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			46
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			43
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	470283
5°	472080
10°	473521
15°	473544
20°	470944
25°	459907
30°	429861
35°	372241
40°	290790
45°	208628
50°	135528
55°	81135
60°	47471
65°	30494
70°	20295
75°	15332
80°	11391
85°	0



TEST NUMBER: P859489

CATALOG NUMBER: LX4C70D010 EX4C709035 4LBWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	364.5	6.1
10°-20°	1050.4	17.7
20°-30°	1550.0	26.1
30°-40°	1529.6	25.8
40°-50°	936.0	15.8
50°-60°	358.9	6.0
60°-70°	112.2	1.9
70°-80°	32.9	0.6
80°-90°	4.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2965.0	49.9
0°-40°	4494.6	75.7
0°-60°	5789.5	97.5
0°-90°	5939.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5939.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3828	
5°	3828	365
15°	3723	1050
25°	3393	1550
35°	2482	1530
45°	1201	936
55°	379	359
65°	105	112
75°	32	33
85°	0	4
90°	0	



TEST NUMBER: P859489

CATALOG NUMBER: LX4C70D010 EX4C709035 4LBWH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3828.0
2.5°	3836.1
5°	3828.0
7.5°	3820.0
10°	3795.8
12.5°	3763.5
15°	3723.2
17.5°	3674.8
20°	3602.2
22.5°	3521.9
25°	3392.8
27.5°	3231.5
30°	3030.2
32.5°	2780.5
35°	2482.0
37.5°	2151.6
40°	1813.2
42.5°	1498.9
45°	1200.8
47.5°	934.6
50°	709.1
52.5°	524.0
55°	378.8
57.5°	265.8
60°	193.2
62.5°	145.2
65°	104.9
67.5°	80.7
70°	56.5
72.5°	40.3
75°	32.3
77.5°	16.1
80°	16.1
82.5°	8.1
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)