

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859498

Luminaire Tested: **LD4C70D010 EU4709040 4LBMLI**

Issue Date: 7/19/2024

**Test Information**

Test Method: LM-79-08  
Report Number: P859498  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208178)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/19/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD4C70D010 EU4709040 4LBMLI  
Description: 4 INCH 7000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS  
AND 4LBM TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6676.0 lumens  
Efficiency: N/A  
Efficacy: 85.6 lumens/watt  
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 78  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P859498

CATALOG NUMBER: LD4C70D010 EU4709040 4LBMLI

### Luminous Intensity Polar Plot





TEST NUMBER: P859498

CATALOG NUMBER: LD4C70D010 EU4709040 4LBMLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88			
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83			
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78			
5	94	87	81	77	93	86	81	77	84	79	76	82	78	75	81	77	75	73			
6	90	82	76	72	89	81	76	72	80	75	71	78	74	71	77	73	71	69			
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65			
8	82	73	68	64	81	73	67	64	72	67	64	71	66	63	70	66	63	62			
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	67	63	60	58			
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	64	60	57	56			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1292947
5°	1270977
10°	1167822
15°	977994
20°	783526
25°	629553
30°	468645
35°	267723
40°	125653
45°	53356
50°	16991
55°	8653
60°	5946
65°	4709
70°	2910
75°	0
80°	0
85°	0



TEST NUMBER: P859498

CATALOG NUMBER: LD4C70D010 EU4709040 4LBMLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	952.9	14.3
10°-20°	2130.4	31.9
20°-30°	2118.0	31.7
30°-40°	1153.4	17.3
40°-50°	266.6	4.0
50°-60°	37.5	0.6
60°-70°	14.0	0.2
70°-80°	3.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5201.3	77.9
0°-40°	6354.7	95.2
0°-60°	6658.9	99.7
0°-90°	6676.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6676.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	10524	
5°	10306	953
15°	7689	2130
25°	4644	2118
35°	1785	1153
45°	307	267
55°	40	38
65°	16	14
75°	0	3
85°	0	0
90°	0	



TEST NUMBER: P859498

CATALOG NUMBER: LD4C70D010 EU4709040 4LBMLI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	10524.3
2.5°	10500.0
5°	10306.1
7.5°	9910.5
10°	9361.4
12.5°	8553.7
15°	7689.4
17.5°	6833.2
20°	5993.1
22.5°	5306.6
25°	4644.3
27.5°	4014.4
30°	3303.6
32.5°	2512.1
35°	1785.1
37.5°	1203.3
40°	783.5
42.5°	492.6
45°	307.1
47.5°	177.8
50°	88.9
52.5°	48.5
55°	40.4
57.5°	24.2
60°	24.2
62.5°	16.2
65°	16.2
67.5°	8.1
70°	8.1
72.5°	8.1
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)