

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859502

Luminaire Tested: **LX4C70D010 EX4C709040 4LBMDLI**

Issue Date: 2/18/2022



Test Information

Test Method: LM-79-08
Report Number: P859502
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-8)
Test Lab: INNOVATION CENTER
Issue Date: 2/18/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C70D010 EX4C709040 4LBMDLI
Description: 4 INCH 7000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 4LRMD45 TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5880.0 lumens
Efficiency: N/A
Efficacy: 75.4 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.82
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 78
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859502

CATALOG NUMBER: LX4C70D010 EX4C709040 4LBMDLI

Luminous Intensity Polar Plot





TEST NUMBER: P859502

CATALOG NUMBER: LX4C70D010 EX4C709040 4LBMDLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | | | | | | | | | | | | | | | | |
| 1 | 114 | 111 | 109 | 107 | 111 | 109 | 107 | 105 | 105 | 103 | 102 | 101 | 100 | 99 | 98 | 97 | 96 | 94 | | | | | | | | | | | | | | | | | | | |
| 2 | 109 | 104 | 100 | 97 | 107 | 102 | 99 | 96 | 99 | 96 | 94 | 96 | 94 | 92 | 94 | 92 | 90 | 88 | | | | | | | | | | | | | | | | | | | |
| 3 | 104 | 98 | 93 | 89 | 102 | 96 | 92 | 89 | 94 | 90 | 87 | 91 | 88 | 86 | 89 | 87 | 85 | 83 | | | | | | | | | | | | | | | | | | | |
| 4 | 99 | 92 | 87 | 83 | 97 | 91 | 86 | 82 | 89 | 85 | 81 | 87 | 83 | 80 | 85 | 82 | 79 | 78 | | | | | | | | | | | | | | | | | | | |
| 5 | 94 | 87 | 81 | 77 | 93 | 86 | 81 | 77 | 84 | 79 | 76 | 82 | 78 | 75 | 81 | 77 | 75 | 73 | | | | | | | | | | | | | | | | | | | |
| 6 | 90 | 82 | 76 | 72 | 89 | 81 | 76 | 72 | 80 | 75 | 71 | 78 | 74 | 71 | 77 | 73 | 70 | 69 | | | | | | | | | | | | | | | | | | | |
| 7 | 86 | 77 | 72 | 68 | 85 | 77 | 71 | 68 | 75 | 71 | 67 | 74 | 70 | 67 | 73 | 69 | 67 | 65 | | | | | | | | | | | | | | | | | | | |
| 8 | 82 | 73 | 68 | 64 | 81 | 73 | 67 | 64 | 72 | 67 | 63 | 71 | 66 | 63 | 70 | 66 | 63 | 62 | | | | | | | | | | | | | | | | | | | |
| 9 | 79 | 70 | 64 | 60 | 78 | 69 | 64 | 60 | 68 | 63 | 60 | 67 | 63 | 60 | 66 | 63 | 60 | 58 | | | | | | | | | | | | | | | | | | | |
| 10 | 75 | 66 | 61 | 57 | 74 | 66 | 61 | 57 | 65 | 60 | 57 | 64 | 60 | 57 | 63 | 59 | 57 | 55 | | | | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 948785 |
| 5° | 981119 |
| 10° | 991053 |
| 15° | 892753 |
| 20° | 741912 |
| 25° | 582068 |
| 30° | 425974 |
| 35° | 220135 |
| 40° | 104548 |
| 45° | 36781 |
| 50° | 8314 |
| 55° | 5398 |
| 60° | 3784 |
| 65° | 2849 |
| 70° | 2012 |
| 75° | 1329 |
| 80° | 990 |
| 85° | 0 |



TEST NUMBER: P859502

CATALOG NUMBER: LX4C70D010 EX4C709040 4LBMDLI

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 759.9 | 12.9 |
| 10°-20° | 1933.4 | 32.9 |
| 20°-30° | 1956.3 | 33.3 |
| 30°-40° | 997.3 | 17.0 |
| 40°-50° | 195.5 | 3.3 |
| 50°-60° | 23.6 | 0.4 |
| 60°-70° | 9.8 | 0.2 |
| 70°-80° | 3.5 | 0.1 |
| 80°-90° | 0.6 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 4649.6 | 79.1 |
| 0°-40° | 5646.9 | 96.0 |
| 0°-60° | 5866.1 | 99.8 |
| 0°-90° | 5880.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 5880.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 7723 | |
| 5° | 7956 | 760 |
| 15° | 7019 | 1933 |
| 25° | 4294 | 1956 |
| 35° | 1468 | 997 |
| 45° | 212 | 196 |
| 55° | 25 | 24 |
| 65° | 10 | 10 |
| 75° | 3 | 4 |
| 85° | 0 | 1 |
| 90° | 0 | |



TEST NUMBER: P859502

CATALOG NUMBER: LX4C70D010 EX4C709040 4LBMDLI

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 7722.9 |
| 2.5° | 7794.4 |
| 5° | 7955.7 |
| 7.5° | 8048.2 |
| 10° | 7944.4 |
| 12.5° | 7595.4 |
| 15° | 7019.2 |
| 17.5° | 6339.3 |
| 20° | 5674.8 |
| 22.5° | 4986.5 |
| 25° | 4294.0 |
| 27.5° | 3604.2 |
| 30° | 3002.8 |
| 32.5° | 2262.6 |
| 35° | 1467.8 |
| 37.5° | 982.7 |
| 40° | 651.9 |
| 42.5° | 409.3 |
| 45° | 211.7 |
| 47.5° | 75.7 |
| 50° | 43.5 |
| 52.5° | 32.2 |
| 55° | 25.2 |
| 57.5° | 19.6 |
| 60° | 15.4 |
| 62.5° | 12.6 |
| 65° | 9.8 |
| 67.5° | 7.0 |
| 70° | 5.6 |
| 72.5° | 4.2 |
| 75° | 2.8 |
| 77.5° | 2.8 |
| 80° | 1.4 |
| 82.5° | 1.4 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)