

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859519

Luminaire Tested: **LD4C70D010 EU4709050 4LBMLI**

Issue Date: 7/19/2024

Test Information

Test Method: LM-79-08
Report Number: P859519
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208178)
Test Lab: INNOVATION CENTER
Issue Date: 7/19/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C70D010 EU4709050 4LBMLI
Description: 4 INCH 7000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS
AND 4LBM TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6813.0 lumens
Efficiency: N/A
Efficacy: 87.3 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 78
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859519

CATALOG NUMBER: LD4C70D010 EU4709050 4LBMLI

Luminous Intensity Polar Plot





TEST NUMBER: P859519

CATALOG NUMBER: LD4C70D010 EU4709050 4LBMLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88			
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83			
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78			
5	94	87	81	77	93	86	81	77	84	79	76	82	78	75	81	77	75	73			
6	90	82	76	72	89	81	76	72	80	75	71	78	74	71	77	73	71	69			
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65			
8	82	73	68	64	81	73	67	64	72	67	64	71	66	63	70	66	63	62			
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	67	63	60	58			
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	64	60	57	56			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1319483
5°	1297059
10°	1191787
15°	998064
20°	799606
25°	642471
30°	478263
35°	273227
40°	128235
45°	54450
50°	17335
55°	8825
60°	6069
65°	4796
70°	2945
75°	0
80°	0
85°	0



TEST NUMBER: P859519

CATALOG NUMBER: LD4C70D010 EU4709050 4LBMLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	972.5	14.3
10°-20°	2174.1	31.9
20°-30°	2161.5	31.7
30°-40°	1177.1	17.3
40°-50°	272.1	4.0
50°-60°	38.3	0.6
60°-70°	14.2	0.2
70°-80°	3.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5308.1	77.9
0°-40°	6485.2	95.2
0°-60°	6795.5	99.7
0°-90°	6813.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6813.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10740	
5°	10518	972
15°	7847	2174
25°	4740	2162
35°	1822	1177
45°	313	272
55°	41	38
65°	16	14
75°	0	3
85°	0	0
90°	0	



TEST NUMBER: P859519

CATALOG NUMBER: LD4C70D010 EU4709050 4LBMLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	10740.3
2.5°	10715.5
5°	10517.6
7.5°	10113.9
10°	9553.5
12.5°	8729.2
15°	7847.2
17.5°	6973.4
20°	6116.1
22.5°	5415.5
25°	4739.6
27.5°	4096.8
30°	3371.4
32.5°	2563.6
35°	1821.8
37.5°	1228.0
40°	799.6
42.5°	502.7
45°	313.4
47.5°	181.4
50°	90.7
52.5°	49.5
55°	41.2
57.5°	24.7
60°	24.7
62.5°	16.5
65°	16.5
67.5°	8.2
70°	8.2
72.5°	8.2
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)