

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859527

Luminaire Tested: **LX4C70D010 EX4C709050 4LBNLI**

Issue Date: 1/21/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P859527  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/21/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX4C70D010 EX4C709050 4LBNLI  
Description: 4 INCH 7000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS  
AND 4LBN TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver:

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5345.9 lumens  
Efficiency: N/A  
Efficacy: 68.5 lumens/watt  
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 78  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P859527

CATALOG NUMBER: LX4C70D010 EX4C709050 4LBNLI

### Luminous Intensity Polar Plot





TEST NUMBER: P859527

CATALOG NUMBER: LX4C70D010 EX4C709050 4LBNLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	92	90	90	90	90
3	105	99	95	92	103	98	94	91	95	92	89	93	90	88	91	89	87	85	85	85	85
4	101	94	89	86	99	93	88	85	91	87	84	89	86	83	87	84	82	81	81	81	81
5	96	89	84	80	95	88	84	80	87	82	79	85	81	79	83	80	78	77	77	77	77
6	92	85	80	76	91	84	79	76	83	78	75	81	78	75	80	77	74	73	73	73	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	69	69	69	69
8	85	77	72	68	84	77	72	68	76	71	68	75	71	68	74	70	67	66	66	66	66
9	82	74	69	65	81	73	68	65	72	68	65	72	68	65	71	67	64	63	63	63	63
10	79	71	66	62	78	70	65	62	69	65	62	69	65	62	68	64	62	61	61	61	61

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1690157
5°	1520964
10°	1179087
15°	853414
20°	590922
25°	430790
30°	313012
35°	185221
40°	77910
45°	24289
50°	3154
55°	1756
60°	2015
65°	2384
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P859527

CATALOG NUMBER: LX4C70D010 EX4C709050 4LBNLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1084.2	20.3
10°-20°	1856.1	34.7
20°-30°	1475.2	27.6
30°-40°	780.9	14.6
40°-50°	134.5	2.5
50°-60°	10.0	0.2
60°-70°	5.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4415.4	82.6
0°-40°	5196.3	97.2
0°-60°	5340.9	99.9
0°-90°	5345.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5345.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	13758	
5°	12333	###
15°	6710	1856
25°	3178	1475
35°	1235	781
45°	140	135
55°	8	10
65°	8	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P859527

CATALOG NUMBER: LX4C70D010 EX4C709050 4LBNLI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	13757.5
2.5°	13403.3
5°	12333.2
7.5°	10933.7
10°	9451.7
12.5°	8019.1
15°	6709.9
17.5°	5491.4
20°	4519.9
22.5°	3778.9
25°	3178.0
27.5°	2692.3
30°	2206.5
32.5°	1712.5
35°	1235.0
37.5°	815.2
40°	485.8
42.5°	280.0
45°	139.8
47.5°	49.5
50°	16.5
52.5°	16.5
55°	8.2
57.5°	8.2
60°	8.2
62.5°	8.2
65°	8.2
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)