

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P#

Luminaire Tested: **LD4C65D010 EX4C659035 4LBSQH**

Issue Date: 2/9/2022



Test Information

Test Method: LM-79-08
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER
Issue Date: 2/9/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C65D010 EX4C659035 4LBSQH
Description: 4 INCH 6500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 4LBSQ TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5386.0 lumens
Efficiency: N/A
Efficacy: 74.4 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P#
CATALOG NUMBER: LD4C65D010 EX4C659035 4LBSQH

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LD4C65D010 EX4C659035 4LBSQH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79			
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73			
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67			
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62			
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58			
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54			
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50			
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	515309
5°	507824
10°	486605
15°	459596
20°	429003
25°	389444
30°	325145
35°	235559
40°	147446
45°	84289
50°	43952
55°	24628
60°	15689
65°	9292
70°	6884
75°	3020
80°	4501
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LD4C65D010 EX4C659035 4LBSQH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	491.4	9.1
10°-20°	1289.2	23.9
20°-30°	1656.8	30.8
30°-40°	1246.6	23.1
40°-50°	500.7	9.3
50°-60°	142.3	2.6
60°-70°	45.1	0.8
70°-80°	12.8	0.2
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3437.5	63.8
0°-40°	4684.0	87.0
0°-60°	5327.0	98.9
0°-90°	5386.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5386.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5341	
5°	5243	491
15°	4601	1289
25°	3658	1657
35°	2000	1247
45°	618	501
55°	146	142
65°	41	45
75°	8	13
85°	0	1
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LD4C65D010 EX4C659035 4LBSQH

CANDELA DISTRIBUTION (FULL):

	0°
0°	5340.6
2.5°	5308.0
5°	5243.0
7.5°	5121.0
10°	4966.5
12.5°	4779.8
15°	4600.9
17.5°	4397.6
20°	4178.0
22.5°	3942.6
25°	3658.0
27.5°	3316.4
30°	2918.3
32.5°	2471.0
35°	1999.8
37.5°	1560.6
40°	1170.6
42.5°	861.6
45°	617.7
47.5°	422.9
50°	292.8
52.5°	203.3
55°	146.4
57.5°	105.7
60°	81.3
62.5°	56.9
65°	40.7
67.5°	32.5
70°	24.4
72.5°	16.3
75°	8.1
77.5°	8.1
80°	8.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)