

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859558

Luminaire Tested: **LX4C75D010 EX4C759030 4LBMH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P859558
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C75D010 EX4C759030 4LBMH
Description: 4 INCH 7500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBM TRIM WITH H FINISH
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6195.0 lumens
Efficiency: N/A
Efficacy: 76.0 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 81.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859558

CATALOG NUMBER: LX4C75D010 EX4C759030 4LBMH

Luminous Intensity Polar Plot





TEST NUMBER: P859558

CATALOG NUMBER: LX4C75D010 EX4C759030 4LBMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91			91
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82			82
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			67
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			61
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55			55
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50			50
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46			46
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43			43
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39			39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	490554
5°	492428
10°	493930
15°	493957
20°	491235
25°	479725
30°	448388
35°	388289
40°	303315
45°	217628
50°	141376
55°	84626
60°	49535
65°	31802
70°	21157
75°	15996
80°	11886
85°	0



TEST NUMBER: P859558

CATALOG NUMBER: LX4C75D010 EX4C759030 4LBMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	380.3	6.1
10°-20°	1095.7	17.7
20°-30°	1616.8	26.1
30°-40°	1595.6	25.8
40°-50°	976.4	15.8
50°-60°	374.3	6.0
60°-70°	117.0	1.9
70°-80°	34.3	0.6
80°-90°	4.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3092.8	49.9
0°-40°	4688.3	75.7
0°-60°	6039.1	97.5
0°-90°	6195.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6195.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3993	
5°	3993	380
15°	3884	1096
25°	3539	1617
35°	2589	1596
45°	1253	976
55°	395	374
65°	109	117
75°	34	34
85°	0	5
90°	0	



TEST NUMBER: P859558

CATALOG NUMBER: LX4C75D010 EX4C759030 4LBMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3993.0
2.5°	4001.5
5°	3993.0
7.5°	3984.6
10°	3959.4
12.5°	3925.7
15°	3883.7
17.5°	3833.2
20°	3757.4
22.5°	3673.7
25°	3539.0
27.5°	3370.8
30°	3160.8
32.5°	2900.3
35°	2589.0
37.5°	2244.4
40°	1891.3
42.5°	1563.6
45°	1252.6
47.5°	974.9
50°	739.7
52.5°	546.6
55°	395.1
57.5°	277.3
60°	201.6
62.5°	151.5
65°	109.4
67.5°	84.1
70°	58.9
72.5°	42.1
75°	33.7
77.5°	16.8
80°	16.8
82.5°	8.4
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)