

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859574

Luminaire Tested: **LX4C75D010 EX4C759035 4LBNH**

Issue Date: 2/8/2022

**Test Information**

Test Method: LM-79-08  
Report Number: P859574  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/8/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX4C75D010 EX4C759035 4LBNH  
Description: 4 INCH 7500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS  
AND 4LBN TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver:


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5220.0 lumens  
Efficiency: N/A  
Efficacy: 64.0 lumens/watt  
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 81.5  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P859574

CATALOG NUMBER: LX4C75D010 EX4C759035 4LBNH

### Luminous Intensity Polar Plot





TEST NUMBER: P859574

CATALOG NUMBER: LX4C75D010 EX4C759035 4LBNH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	74	65	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	805169
5°	787255
10°	727896
15°	653145
20°	574946
25°	494812
30°	398453
35°	265263
40°	137986
45°	62460
50°	27102
55°	18185
60°	11647
65°	8285
70°	6825
75°	4509
80°	0
85°	0



TEST NUMBER: P859574

CATALOG NUMBER: LX4C75D010 EX4C759035 4LBNH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	591.3	11.3
10°-20°	1434.4	27.5
20°-30°	1665.3	31.9
30°-40°	1102.8	21.1
40°-50°	309.3	5.9
50°-60°	77.7	1.5
60°-70°	29.2	0.6
70°-80°	10.0	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3691.0	70.7
0°-40°	4793.8	91.8
0°-60°	5180.8	99.2
0°-90°	5220.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5220.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	6554	
5°	6384	591
15°	5135	1434
25°	3650	1665
35°	1769	1103
45°	360	309
55°	85	78
65°	28	29
75°	10	10
85°	0	0
90°	0	



TEST NUMBER: P859574

CATALOG NUMBER: LX4C75D010 EX4C759035 4LBNH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	6553.9
2.5°	6525.5
5°	6383.7
7.5°	6137.5
10°	5834.9
12.5°	5494.4
15°	5135.3
17.5°	4785.3
20°	4397.7
22.5°	4038.2
25°	3650.3
27.5°	3281.7
30°	2808.8
32.5°	2307.5
35°	1768.7
37.5°	1267.3
40°	860.4
42.5°	557.8
45°	359.5
47.5°	217.7
50°	141.8
52.5°	103.9
55°	84.9
57.5°	66.4
60°	47.4
62.5°	37.9
65°	28.5
67.5°	19.0
70°	19.0
72.5°	9.5
75°	9.5
77.5°	9.5
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)